



171436522509
ON/OFF CONTROL ROCKER SWITCH 2-POL, 250V POLAR WHITE GLOSSY, INTEGRO

Product Properties:

Nominal voltage	250 V
Connection type	Screwed terminal
Rated current	10 A
Mounting method	Built-in installation
Anti-bacterial treatment	No
Surface finishing	Glossy
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Assembly arrangement	Basic element with central cover plate
Wiring system	2-pole switch
Method of operation	Rocker/button
With mounting plate	No
Label space/information surface	Yes
Illumination	No
Feedback-signal contact	No
Heating switch	No
Washing machine switch	No
Type of fastening	Screw mounting
RAL-number (similar)	9010 .
Min. depth of built-in installation box	16 mm
Colour	White
Material	Plastic
Type of product	Strömbrytare
Variant	250V
Built-in depth	15.5 mm

Dimensions:

Built-in depth	15.5 mm
Number of modules (module system)	1 .
Device width	55.5 mm
Device height	55.5 mm
Device depth	25 mm
Number of rockers	1 .
Switching current for fluorescent lamps	10 AX
Min. depth of built-in installation box	16 mm
MOQ	10 .
Unit	pcs
Nominal voltage	250 V

Approvals:

Compliance:

REACH	No SVHC (Latest. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC001590 - Installation switch
ETIM-Release	9.0

Trademark	Berker
Product Group	Installation switches
Search Description	936522509
Alternative SKU	171436522509
<u>Logistic information:</u>	
Barcode	401133424004
Country of origin	DE
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	171436522509
Taric code	85365080
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.