
# 0138 : Viragrip® in Heavy Duty Cast Iron












## The + product :

**High effort resistance:** reinforced model.
**Efficient:** self-clamping on pipe.
**Fast:** moving jaw ratchet effect.

## Description

Viragrip® pipe wrench, 6" to 48", for tubes of Ø 3/4" to 6".

Reinforced handle and head for use in extreme tightening conditions. Moving jaw made from treated forged steel, with 2 springs allowing effective self-tightening of the tube and providing clamping force identical to that of a ratchet. High-frequency double hardening for gear teeth.

In accordance with standard US/GGG-W-651-E.

HEAVY DUTY: + 30% more strength.

## References

| Sku | A " | A mm | L " | L mm | E mm | kg |
|---|---|---|---|---|---|---|
| **013806** | 3/4 | 27 | 6 | 150 | 15 | 0,240 |
| **013808** | 1 | 34 | 8 | 200 | 15 | 0,400 |
| **013810** | 1.3/4 | 55 | 10 | 250 | 20 | 0,770 |
| **013812** | 2 | 60 | 12 | 300 | 25 | 1,110 |
| **013814** | 2 | 60 | 14 | 350 | 25 | 1,610 |
| **013818** | 2.1/2 | 76 | 18 | 450 | 30 | 2,580 |
| **013824** | 3.1/2 | 102 | 24 | 600 | 30 | 3,740 |

| Sku | A " | A mm | L " | L mm | E mm | kg |
|---|---|---|---|---|---|---|
| **013836** | 5 | 140 | 36 | 900 | 40 | 7,750 |
| **013848** | 6 | 168 | 48 | 1200 | 52 | 14,100 |