

Bourdon tube pressure gauges,model 111

Model: 111.10 - 8990471

Specifications according to data sheet

Model: 111.10 standard bottom

Nominal size: 063 mm

Unit of outer Scale: psi / -inHg

Measuring range: vacuum- or compound-range

Scale range: -30...0 inHg

2nd Scale or Special Scale: 2nd scale kPa

Process connection: 1/4 NPT

Connector location: lower mount

Case: black plastic

Window: plastic, clear

Accuracy class: class 2.5

Pointer: plastic, black (double division)

Packaging: standard packing

Dial: plastic, white, with stop-pin

Specifications according to data sheet: PM 01.01

Dial description:

Pressure Gauge Standard: International (standard Europe)

color for 1.scale (outside): black

color for 2.scale (inside): red RAL 3020

dial background: White

Manufacturer logo: *WIKA*

stop pin on dial: at zero

norm-mark on dial: *EN 837-1*

accuracy class on dial: *Cl.2.5*accuracy class on dial: *Cl.1.6*

