


PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Wood drills
Catalogue number	3035, 3040
Date	09/07/2008

Range Description A range of professional quality wood drill bits				
Features <ul style="list-style-type: none"> • Chrome vanadium steel for a long life • Brad pointed for accurate drill starts • Spur ground external edge cut clean hole cutting 				
Item Number	Item Description (Drill bits size = Diameter x working length x overall length)	EAN No	Commodity code	Carton Qty
T3035 03	Wood Drill Bit 3x33x61mm	5013969438208	82075090	10
T3035 04	Wood Drill Bit 4x43x75mm	5013969438307	82075090	10
T3035 05	Wood Drill Bit 5x52x86mm	5013969438406	82075090	5
T3035 06	Wood Drill Bit 6x60x97mm	5013969438505	82075090	5
T3035 08	Wood Drill Bit 8x75x117mm	5013969438604	82075090	5
T3035 10	Wood Drill Bit 10x87x133mm	5013969438802	82075090	5
T3035 12	Wood Drill Bit 12x96x151mm	5013969439007	82075090	5
T3035 13	Wood Drill Bit 13x96x151mm	5013969439106	82075090	5
T3035 14	Wood Drill Bit 14x97x151mm	5013969439205	82075090	5
T3035 16	Wood Drill Bit 16x100x160mm	5013969439304	82075090	3
T3040	Wood Drill Bit Set of 5	5013969844900	82075090	70

Technical product information	
Standards compliance	
User health and safety information	Users and bystanders are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Drills are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3035 03	3	3	61	3	48	9	168	9
T3035 04	4	4	75	5	48	9	168	12
T3035 05	5	5	86	9	48	9	197	15
T3035 06	6	6	97	14	48	8	197	21
T3035 08	8	8	117	28	48	11	232	36
T3035 10	10	10	133	47	48	14	232	56
T3035 12	12	12	151	72	48	18	232	82
T3035 13	13	13	151	82	48	18	232	92
T3035 14	14	14	151	91	48	18	232	101
T3035 16	16	16	160	121	48	18	232	132
T3040	-	-	-	-	56	18	158	173

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3035 03	168	106	27	117		
T3035 04	168	106	27	145		
T3035 05	197	83	28	102		

T3035 06	197	83	28	128		
T3035 08	232	100	25	215		
T3035 10	232	100	25	315		
T3035 12	232	100	25	442		
T3035 13	232	100	25	499		
T3035 14	232	100	57	545		
T3035 16	232	100	57	435		
T3040	400	300	120	9972		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3035 03	2	Blister	5	Card			27	Box
T3035 04	2	Blister	5	Card			27	Box
T3035 05	2	Blister	5	Card			27	Box
T3035 06	2	Blister	5	Card			27	Box
T3035 08	2	Blister	6	Card			36	Box
T3035 10	2	Blister	7	Card			36	Box
T3035 12	2	Blister	7	Card			36	Box
T3035 13	2	Blister	7	Card			42	Box
T3035 14	2	Blister	7	Card			42	Box
T3035 16	2	Blister	7	Card			42	Box
T3040							389	Box