



# Heat Gun

## HG5030K/2

1 600 W • 300 / 500 l/min • 350 / 500 °C

### Heat gun with two heat and air flow settings

A basic 1 600 W heat gun for demanding use in a wide range of applications, including paint stripping. The heat gun has two heat and air flow settings.

### Technical specifications

Continuous Input Power 240V	1600 W
Maximum Flow Rate	300 / 500 L/min
Temperature Range	350 - 500 °C
Max. Temperature	500 °C
Variable Temperature	✓
Thermal Safety Switch	✓
Weight Without Cable	0,56 kg
Product Dimensions (L x W x H):	233 x 80 x 208 mm
Power Supply Cord	2,0 m

### User benefits

- Variable temperature control
- The rubber coating on the handle ensures a firm working grip
- With overheat protection

**EAN 0088381857321**

Link to product - [www.makita.uk.com](http://www.makita.uk.com)



# Related products

## Other

User manual

Parts drawing