



Power Strip STRONG 5xT13 GdV 3x1.5mm2 3m with Switch and Mounting Magnets IP21 orange



Item No.: 207620135 K
EAN Code: 7611007138042

Description

Power Strip STRONG 5xT13 transverse with hinged cover, GdV cable H07RN-F 3G1.5mm2, cable length 3m, T12 plug, reset switch (ON/OFF switch with resettable overcurrent protection), mounting eyelets on the back, mounting magnets incl. adhesive metal mounting plates, cable winding device, IP21, orange

Specifications

Type	Industrial Power Strip
Brand	STEFFEN
Model	Strong
Number of Sockets	5
Socket Type	Type 13
Socket Colour	Orange/Blue
Socket Orientation	Transverse
Increased Touch Protection	No
Switch	Yes
Rated Current	10 A
Rated Voltage	230 V
Rated Frequency	50 - 60 Hz
Rated Power	2300 W

Cable Type	H07RN-F (GdV)
Number of Conductors	3
Conductor Cross-Section	1.5 mm ²
Cable Length	3 m
Cable Colour	Black
Plug Type	Type 12
Mounting Option	Mounting Magnets
Main Material	Plastic
Halogen-Free	No
UV Resistance	No
Product Colour	Orange
Application	Indoor, Outdoor
K2 Suitable for Construction Sites	Yes
IP Rating	IP21
Operating Temperature Range	-25...+55 °C
Safety Features	Overcurrent Circuit Breaker
Additional Features	High-Impact-Resistant Housing
Product Height	380 mm
Product Width	100 mm
Product Depth	60 mm
Net Weight	1.700 Kg
Packaging	Shrink Wrap