

4x4 VGA Matrix Video Switch Splitter with Audio

Product ID: ST424MX



The ST424MX 4x4 VGA Matrix Switcher/Splitter allows users to share up to four distinct VGA inputs (as well as a corresponding audio source) between four independent displays or projectors.

Providing convenient push button control, the VGA Matrix Switcher/Splitter allows each of the four input VGA signals and the corresponding audio, to be switched individually meaning that you can have a different source showing on each display or one source showing on both offering maximum flexibility and control.

To ensure optimized VGA distribution and signal management even over longer distance signal transmissions, the ST424MX VGA Matrix Switcher/Splitter features a built-in signal booster that facilitates installation of displays at distances of up to 210ft away from the source device, while maintaining flawless signal integrity.

Designed to provide maximum control while saving space and eliminating clutter, the ST424MX can be used as a standalone solution or rack mounted using the (included) ear-mounts.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Take full control of your sources and displays/projectors - select any source on any display
- Run multimedia presentations with supporting data showing on another display in business conference rooms or at trade-shows
- Perfect for digital signage applications in retail environments requiring more than one media player or PC to be connected
- Allow trainees/students to see what is on your display and then switch them back to their own display after the demonstration completes
- Ideal for connecting/switching multiple sources in Test Bench Facilities, Data Centers, Help Desks and Video Broadcasting Facilities

Features

- Allows four PC's / Media Players to provide video to four displays / projectors
- Supports cascading with additional units
- Maximum resolution of up to 1920 x 1440 pixels
- 65m (213ft) Maximum cable length
- Equipped with easy to use front panel selection buttons
- High video bandwidth (350 Mhz)
- Supports Multi-Sync video types including RGBHV, RGsB, RGSB
- Supports DDC, DDC2, DDC2B
- Audio Frequency Response 20Hz~20KHz

Hardware	Warranty	2 Years
	Audio	Yes
	AV Input	VGA
	AV Output	VGA
	Daisy-Chain	Yes
	Industry Standards	DDC, DDC2, DDC2B
	Ports	4
	Rack-Mountable	Yes
Performance	Bandwidth	350 MHz
	Maximum Analog Resolutions	1920x1440 @ 85Hz
	Maximum Cable Length	65 m [213.2 ft]
Connector(s)	Connector A	4 - 3.5 mm Mini-Jack (3 Position) Female
		4 - VGA (15 pin, High Density D-Sub) Female
	Connector B	4 - 3.5 mm Mini-Jack (3 Position) Female
		4 - VGA (15 pin, High Density D-Sub) Female
Power	Center Tip Polarity	Positive
	Input Current	0.3A
	Input Voltage	100 - 240 AC
	Output Current	1.25A
	Output Voltage	12 DC
	Power Consumption (In Watts)	15
	Power Source	AC Adapter Included
Physical Characteristics	Color	Black
	Product Height	4.2 cm [1.7 in]
	Product Length	26.9 cm [10.6 in]
	Product Width	10.8 cm [4.3 in]
	Weight of Product	1.1 kg [2.3 lb]
Packaging Information	Package Height	27.9 cm [11 in]
	Package Length	35.7 cm [14.1 in]
	Package Width	82 mm [3.2 in]

	Shipping (Package) Weight	1.8 kg [3.9 lb]
What's in the Box	Included in Package	1 - VGA 4x4 Matrix Switch 2 - Ear-mounts for rack-mounting 1 - Bag of Screws 1 - Universal Power Adapter (US/UK/EU/AUS) 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.