



Pushing Performance  
Since 1945

# Han 24HPR-HTE4-SCL-M20-enlarged



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 40 024 0453                                                                |
| Specification      | Han 24HPR-HTE4-SCL-M20-enlarged                                               |
| HARTING eCatalogue | <a href="https://harting.com/19400240453">https://harting.com/19400240453</a> |

## Identification

|                          |                               |
|--------------------------|-------------------------------|
| Category                 | Hoods / Housings              |
| Series of hoods/housings | Han <sup>®</sup> HPR enlarged |
| Type of hood/housing     | Hood                          |

## Version

|                         |                                                                                                                                                |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Size                    | 24 HPR enlarged                                                                                                                                |
| Version                 | Top entry                                                                                                                                      |
| Number of cable entries | 4                                                                                                                                              |
| Cable entry             | 4x M20                                                                                                                                         |
| Locking type            | Screw locking                                                                                                                                  |
| Field of application    | Hoods/housings for harsh outdoor environments                                                                                                  |
| Details                 | When using Han <sup>®</sup> Standard inserts of size B or Han-Modular <sup>®</sup> hinged frames, please order adapter 09400009960 separately. |

## Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Tightening torque (screw locking)      | 4 Nm                                           |
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65<br>IP68<br>IP69 / IPX9K acc. to ISO 20653 |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12                                  |



**Pushing Performance**  
Since 1945

## Material properties

|                         |                                           |
|-------------------------|-------------------------------------------|
| Material (hood/housing) | Aluminium die-cast<br>Corrosion resistant |
| Surface (hood/housing)  | Powder-coated                             |
| Colour (hood/housing)   | RAL 9005 (jet black)                      |
| Material (locking)      | Stainless steel                           |

## Specifications and approvals

|           |                                                            |
|-----------|------------------------------------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL                                               |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 797.67 g                                 |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140173262                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |