



PRODUCT-DETAILS

BVND-P130GT-11
COND FTNG STR PG13.5 NW10 IP66 BLK



General Information	
Extended Product Type:	BVND-P130GT-11
Product ID:	7TAA292150R0187
EAN:	7630030213434
Catalog Description:	COND FTNG STR PG13.5 NW10 IP66 BLK
Long Description:	VN Straight Connector for IP66 Static Conduit - Thread PG 13.5, Fits to Conduit Size NW/Metric 10/12, Thread Length 11.0, Color Black
Display Name:	BVND-P130GT-11

Additional Information	
Product Main Type:	PMA Flexible Cable Protection
Application:	Use In Railway Vehicle and Heavy Machine Construction
Product Type:	Fittings for Nylon Flexible Conduits

Ordering

EAN:	7630030213434
UPC:	786209951496

Technical

Number of Batteries:	0
Color:	Black
Material:	Polyamide 6
Size:	NW10 , PG13.5 Thread

Environmental

WEEE Category:	Product Not in WEEE Scope
----------------	---------------------------

Container Information

Package Level 1 Units:	100 EA
Package Level 1 EAN:	7630030213434
Package Level 1 Height:	0 mm 0 in
Package Level 1 Depth / Length:	0 mm 0 in
Package Level 1 Width:	0 mm 0 in

Certificates and Declarations

Data Sheet, Technical Information:	BVND-P130GT-11
Instructions and Manuals:	BVND-P130GT-11
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC001176 - Screw connection for corrugated plastic hose
ETIM 9:	EC001176 - Screw connection for corrugated plastic hose
UNSPSC:	39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

