



Main

Range of product	Mureva Styl
Range	Mureva Styl
Product or component type	Push-button
Category	Push-button with label holder
Device presentation	Insert
Colour tint	White (RAL 9003)

Complementary

Device mounting	Surface Flush
Switch function	Push-button
Actuator	Push-button
Rated current	10 A
[Ue] rated operational voltage	250 V AC
Condition of use	Indoor/Outdoor
Material	Brass SEBS ABS (acrylonitrile butadiene-styrene)
Fixing mode	Screwless
Clamping connection capacity	1.5...2.5 mm ² rigid 1.5...2.5 mm ² flexible 1.5...2.5 mm ² stranded
Wire stripping length	13 mm
Length	71 mm
Height	40 mm
Width	71 mm
Embedding depth	10 mm
Projecting depth	60 mm

Environment

Quality labels	NF CE EAC
----------------	-----------------

AENOR

IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing ≥ 650 °C according to IEC 60695-2-1
Standards	EN 60669-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C