

Cover connection rear, 3VA10 (100 A)



Model	
product brand name	SIVACON S4
product designation	cover plate cable entry
design of the product	3VA10 (100 A), 3VA11 (160 A)
design of the surface	zinc plated
General technical data	
design of pole	4
design	assembly kit
suitability for use	for 3VA molded-case circuit breakers
RAL color number	other
color	miscellaneous
Product details	
product component	
• cable entry	Yes
• lock	No
Mechanical Design	
height	150 mm
width	281 mm
depth	10 mm
installation width for cabinet installation	281 mm
installation depth for cabinet installation	5 mm
shape of inner subdivisions	
• shape 2a	No
• shape 2b	No
• shape 3a	No
• shape 3b	No
• shape 4a	Yes
• shape 4b	Yes
mounting position	horizontal
net weight	0.5 kg
material	sheet-steel
Certificates	
reference code according to IEC 81346-2	UC
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

Environment

[Environmental Conformations](#)

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ5000-4BA80>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ5000-4BA80>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ5000-4BA80

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

1/19/2024 

