

A699 - MR13 ESD PU Palm Glove (Pk12)

Collection: ESD Gloves

Range: Hand Protection

Materials: Polyester, Steel Fibre, Carbon Fibre, Elastane

Dipping:

Inner Pack: 12

Outer Carton: 144

Product information

Level C cut resistant glove for protection against cuts and sharp objects. 13g Polyester and carbon fibre shell which diverts static electricity. A reinforced thumb crotch for added durability. PU palm coating for excellent grip and dexterity. For use in automotive, electronics assembly, testing and precision work. Suitable for use with most touchscreen devices. Sold as a pack of 12 pairs.

ESD Gloves

Designed to dissipate static electricity, the Portwest ESD glove range has been tested to EN16350, a glove specific standard, to ensure protection of electronic devices from the risk of damage by electrostatic phenomena and static charge. Ideal for use in electrical component manufacturing.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (4X42C)

EN 16350:2014 Pass Level R < 1.0 x 108 Ω -

IEC 61340-5-1:2016



Features

- Level C cut resistance
- Seamless 13 gauge liner
- Suitable for use in ESD environments
- Reinforced thumb crotch for extra protection and durability
- Anti-static
- Sold in a pack of 12 pairs
- This glove can be used with most mobile touchscreen devices
- Palm dipped to increase dexterity and ventilation
- Breathable seamless liner
- CE certified
- UKCA marked



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A699 - MR13 ESD PU Palm Glove (Pk12)

Commodity Code: 6116108091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/22832-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A699G6RXS	Grey/White	45.0	28.0	42.0	0.5040	0.0529	5036146015108	15036108850089
A699G6RS	Grey/White	45.0	28.0	42.0	0.5760	0.0529	5036146015085	15036108850065
A699G6RM	Grey/White	45.0	28.0	42.0	0.6240	0.0529	5036146015078	15036108850058
A699G6RL	Grey/White	45.0	28.0	42.0	0.6720	0.0529	5036146015061	15036108850041
A699G6RXL	Grey/White	45.0	28.0	42.0	0.7440	0.0529	5036146015092	15036108850072
A699G6RXXL	Grey/White	45.0	28.0	42.0	0.8160	0.0529	5036146015115	15036108850096