



## BE-8600i - BE-8623i

### ERGO™ Stainless Steel Phillips Screwdrivers with 3-Component Handle PH0-PH4










#### PRODUCT DETAILS

- Screwdriver developed according to the scientific ERGO™ process
- ERGO™ stainless-steel screwdriver for Phillips head screws
- three-component handle for maximum user comfort
- The soft material with ridged surface provides superior grip and greater force transmission
- Flat face to prevent rolling
- Integrated hanging hole
- SS blade protects against formation of rust that can occur when screwdriving jobs on stainless-steel are performed with non-stainless-steel tools
- Easy to choose the right tip with the colour-coded handle and permanent symbol on the domed end
- No colour identification in extra small handle, size PH0
- Standards: ISO 8764, DIN 5260



#### PRODUCT ATTRIBUTES

| Product         |  |  |  |  |  |  |  |
|-----------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| <b>BE-8600I</b> | PH 0                                                                                | 60 mm                                                                               | 3 mm                                                                                | 20 mm                                                                               | 122 mm                                                                                | 182 mm                                                                                | 30 g                                                                                  |
| <b>BE-8610I</b> | PH 1                                                                                | 75 mm                                                                               | 5 mm                                                                                | 27 mm                                                                               | 122 mm                                                                                | 197 mm                                                                                | 62 g                                                                                  |
| <b>BE-8620I</b> | PH 2                                                                                | 100 mm                                                                              | 6 mm                                                                                | 36 mm                                                                               | 122 mm                                                                                | 222 mm                                                                                | 106 g                                                                                 |
| <b>BE-8623I</b> | PH 3                                                                                | 150 mm                                                                              | 8 mm                                                                                | 36 mm                                                                               | 122 mm                                                                                | 272 mm                                                                                | 150 g                                                                                 |

Follow the Fish!

