

Main

Range of product	Harmony Pocket Remote
Product or component type	Hand-held remote control
Device short name	ZART
Control button type	4 single step push-button


Complementary

Material	Push-button cover: silicone rubber Enclosure: ABS + PET
Function available	Power switch
Display type	1 LED
Operating distance	50 m
Communication network type	Wireless
Transmission frequency	2.4 GHz
Maximum sensing distance	300 m in free field
Response time	< 500 ms
Autonomy	> 100 h with alkaline batteries
Battery type	2 AAA/LR3 alkaline
Width	66 mm
Height	114 mm
Depth	37.5 mm
Product weight	0.135 kg

Environment

Radio agreement	IC FCC
IP degree of protection	IP67
Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-20...45 °C
Operating altitude	0...2000 m
Storage altitude	0...3000 m
Relative humidity	0...95 % at -20...60 °C operating
Product certifications	CE

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins