


[Phones With Answering Machine](#)
[Telephones With Single Handset](#)

Telephone KX-TGC220E

General	Colour	S[Silver]
	Handset (Quantity)	1
	Frequency	1.9 GHz
	Frequency Range	1.88 GHz - 1.90 GHz
	Number of Channels	120 Channels
	System	DECT
	DECT Security Mode	-
	GAP	Yes
	Number of Phone Lines	1
	Multiple Handsets Capability	-
	Multiple Base Units Capability	-
	LCD Language	Catalan, Danish, Dutch, English, Finnish, French, German, Greek, Italian, Norwegian, Portuguese, Spanish, Swedish, Turkish
	Wi-Fi® Connection	-
	Mobile Connection	-
	Android™ OS Version	-
Power Saving	Low Radio Power	Yes
	One Touch Eco Mode	Yes
Smartphone Connect	Smartphone Connect	-
	Multiple Smartphones Capability	-
	Supported Devices	-
	Wireless Network Standard	-

	Simplified Configuration	-
	Easy Wi-Fi Setup Button	-
	Wi-Fi Repeater Mode	-
	Phonebook Copy from Smartphone	-
	Ringtone Copy from Smartphone	-
	Wallpaper Image Copy from Smartphone	-
	Conference Call with Outside Landline and Smartphone	-
	Transferring Landline Call (between Smartphone and Handsets)	-
	Playing Answering System Messages	-
Convenience	Key Finder Compatible	-
	Multiple Key Finder Capability	-
	Repeater Available	Yes
	Clear Sound	Yes
	Noise Reduction	-
	Customized Sound System (Equalizer)	-
	Compatible with Hearing Aid T-Coil (TIA-1083 Compliant)	-
	Power Back-Up Operation	-
	Baby Monitor	-
	Smart Function Key	-
	Any Key Answer	Yes

	Do Not Disturb Mode	-
	Bypassing Do Not Disturb Mode (Specified Phonebook Category)	-
	SMS	-
	Call Restriction	Yes
	Distress Call	-
	Conference Call with Outside Line	-
	Call Share	-
	Intercom (Handset to Base Unit)	-
	Intercom (Handset to Handset)	-
	Intercom All	-
	Clock	Yes
	Calendar/Scheduler	-
	Alarm (Wake-up / Memo alarm)	Yes/ Yes
	Advanced Alarm (A day of the week / Snooze)	Yes/ Yes
	Bluetooth® Headset Capability (HSP Support)	-
	Bluetooth Audio Headphone/Speaker Capability (A2DP Support)	-
	Google Play™ Support	-
Caller ID/ Phonebook	Caller ID	Yes/* Requires subscription to Caller ID service offered by your provider/telephone company.
	Caller ID Memory	50 items/* Requires subscription to Caller ID service offered by your provider/telephone company.
	Call Waiting Caller ID	Yes/* Requires subscription to both Caller ID and Call Waiting with Caller ID services offered by your provider/telephone company.

	Category Ringer / Ringer ID	-
	Category Display Colours	-
	Talking Caller ID (Handset)	-
	Talking Caller ID (Base Unit)	-
	Talking Caller ID Language	-
	Nuisance Call Block	Yes (30 numbers)/ * Requires subscription to Caller ID service offered by your provider/telephone company./ * Requires number registration in the nuisance call block list.
	Block Range of Numbers	Yes/ * Requires subscription to Caller ID service offered by your provider/telephone company.
	Block Numberless Call	Yes/ * Requires subscription to Caller ID service offered by your provider/telephone company./ * Numberless calls cannot be blocked depending on the service of your provider/telephone company.
	Handset Phonebook Memory (Name/Number)	-
	Base Unit Phonebook Memory (Name/Number)	50 items/(16char/24digits)
	Shared Phonebook	-
	Phonebook Copy (Handset to Handset)	-
	Phonebook Copy from Mobile Phone via Bluetooth	-
	Speed Dial (Handset)	Yes (6 entries)
	Speed Dial (Base Unit)	-
	Chain Dial	Y(Handset)
Handset	LCD	1.6 inch (4.1 cm)/FullDot Monochrome/103x65 pixels
	LCD Backlight Colour	Amber
	Touchscreen	-
	Front Camera	-
	Rear Camera	-
	LED Flash	-

	GPS	-
	SD Memory Card Slot	-
	USB Jack	-
	USB Version	-
	Illuminated Keypad	-
	Speakerphone (Volume Steps)	Yes (6-step)
	Icon Operation (Number of Icons)	Yes (6)
	Ringer Pattern (Tone+Melody)	15 (5+10)
	Polyphonic Ringer Melody	32 chord
	Ringer Volume Steps	6+OFF
	Receiver Volume Steps	4
	Redial Memory	10(Name & Number)/* Requires registration in the phonebook to display the name.
	Digits of Redial Number	24
	Auto Redial	-
	Ringer Indicator (Colour)	-
	Charge Indication (Colour)	-
	Hold	Yes
	Mute	Yes
	Key Lock	Yes
	Headset Jack	-
	Secure Grip	-
	Short Stroke Key	-
	Wall Mountable (Charger)	-
Base Unit	Dial Keypad	-

	Corded Handset (Power Outage Operation)	-
	Display	-
	Speakerphone (Volume Steps)	-
	Ringer Pattern (Tone+Melody)	1(1+0)
	Ringer Volume Steps	6+OFF
	Redial Memory	-
	Auto Redial	-
	Mobile Locator	-
	Hold	-
	Mute	-
	Handset Locator	Yes
	Wall Mountable	-
Answering System	Answering System	Yes
	Total Recording Time	About 18 min
	Fast-Forwarding and Rewinding Message	-
	Audible Message Alert	-
	New Message Notification by a Call	-
	Announcement Language of New Message Notification	-
	New Message Notification by an SMS	-
	Visual Message List (Handset LCD)	-
	Recording Conversation	-
	Speaker Volume Steps(Base Unit Speaker)	8+OFF

	Call Screening (Handset)	Yes
	Call Screening (Base Unit)	-
	Language of Pre-recorded Greeting Message	English
	Remote Operation from Handset	Yes
	Remote Operation from Outside (DTMF)	Yes
	Toll Saver (New Messages Recorded / No New Message)	2/5
Accessories	Key Finder Included (Quantity)	-
	Repeater Included	-
	Belt Clip Included	-
Optional Handset	Optional Handset	-
Others	Radiation Free (Eco Mode Plus)	-
	Rechargeable Battery	Ni-MH(AAA x 2)
	Talk Time	Up to 16 hours
	Standby Time	Up to 200 hours
	Charge Time	About 7 hours
Power Consumption	Base Unit Standby Power Consumption	0.54 W
	Charger Standby Power Consumption	-
Dimensions/ Weight	Base Unit Dimensions (W x D x H)	Approx. 107 mm x 96 mm x 77 mm
	Handset Dimensions (W x D x H)	Approx. 47 mm x 30 mm x 164 mm
	Charger Dimensions (W x D x H)	-

Key Finder Dimensions (W x D x H)	-
Repeater Dimensions (W x D x H)	-
Base Unit Weight	Approx.120 g
Handset Weight with Battery	Approx. 130 g
Charger Weight	-
Key Finder Weight	-
Repeater Weight	-

Copyright © 2022 Panasonic UK & Ireland