



ENGLISH

Datasheet

RS Pro Weighing Scale, Bench, 3kg Capacity Type G - British 3-pin

RS Stock No: **806-4702**



Product Details

RS Pro weighing scale bench with 3 kg capacity is a professional, highly accurate balance scale with robust cast aluminium housing. The balance is supplied with an AC adapter and RS-232 interface for connection to a PC. It is excellent for any precision weighing task with the built in under hook weighing function.

Features and Benefits

- Stainless steel plate and spill ring for easy cleaning and durability
- High precision strain gauge load cell
- Large, easy to read LCD display with blue backlight
- Parts counting function
- Levelling bubble and adjustable feet for fine adjustment and accurate settings of the scale
- RS232 interface
- Sealed panels for added protection
- Outside calibration for easy setting
- Mains or battery operated with overload protection
- Under hook weighing function

Specifications:

Calibrated	External
Interface Type	RS232
Maximum Operating Temperature	+40°C
Minimum Operating Temperature	+10°C
Net Weight	1.05 kg
Parts Counting	Yes
Plug Type	Type G - British 3-Pin
Scale Type	Bench
Weighing Capacity	3000 g
Weighpan Dimensions	166 x 128 mm
Weighpan Length	166 mm
Weighpan Width	128 mm
Battery Operated	Yes
Display Type	LCD
Platform Material	Stainless Steel