

FEATURES

- Available with 2, 3, 4 & 5 treads
- All supplied with retractable sprung castors within a steel hoof/cover for mobility
- Manufactured from steel offering excellent durability
- Double handrails for increased operator safety
- 50 mm swivel castors under a steel hoof
- Supplied with ribbed rubber anti-slip treads and platform
- Powder coated blue

RS PRO 3 Tread Steel Steps 0.77m Platform Height, Blue

RS Stock No.: 669-3730



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing safety wheel along steps from RS PRO, a range of high quality and mobile safety steps ideal for use in a wide range of environments for working at height and accessing higher environments. The robust design is manufactured from steel, offering excellent durability with ribbed rubber treads and platform for enhanced grip. The steps benefit from sprung fitted retractable castor wheels enclosed in a steel cover, allowing the steps to be manoeuvred with ease whilst maintaining stability when weight is applied whilst in use. The steps also feature a safety hand rail, adding an additional level of safety when in use. The steps are available with a range of treads (steps) including 2, 3, 4 and 5.

What sizes are available?

- 2 Tread: [9097066](#)
- 3 Tread: [6693730](#)
- 4 Tread: [6693734](#)
- 5 Tread: [9097075](#)

General Specifications

Number of Steps	3
Material	Rubber, Steel
Colour	Blue
Applications	Retail, Warehouse, Distribution, Home, Office

Mechanical Specifications

Overall Dimensions	1440mm x 635mm x 805mm
Overall Height	1440mm
Overall Width	635mm
Overall Depth	805mm
Weight	22.5kg

Platform Dimensions	
Height	508mm
Top Tread Width	380mm
Top Tread Depth	280mm



No. Of Treads	Overall H x W x D (mm)	Tread W x D (mm)	Top Tread W x D (mm)	Platform Height (mm)	Average Working Height (mm)	RS Stock No
2	1185 x 580 x 615	380 x 180	380 x 280	508	2000	9097066
3	1440 x 635 x 805	380 x 180	380 x 280	795	2320	6693730
4	1745 x 610 x 1010	380 x 180	380 x 280	1045	2570	6693734
5	1940 x 580 x 1120	380 x 180	380 x 280	1270	2770	9097075

