

## har-port USB 2.0 A-A; PFT 1,5m cable



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1922
Specification	har-port USB 2.0 A-A; PFT 1,5m cable
HARTING eCatalogue	<a href="https://harting.com/09454521922">https://harting.com/09454521922</a>

### Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 2.0

### Version

Cable length	1.5 m
Connection type	Type A jack - type A connector
Fixing	Screwable in cover plates

### Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

### Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	silver
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances Not contained

California Proposition 65 substances Not contained

## Specifications and approvals

Approvals DNV GL

## Commercial data

Packaging size 1

Net weight 64.14 g

Country of origin Germany

European customs tariff number 85444290

GTIN 5713140060593

eCl@ss 27060304 Appliance cord (data cable)

ETIM EC002599

UNSPSC 24.0 43202222