

610813060

Aluminium Enclosure Standard unpainted 80 x 125 x 57 mm

Aluminium Enclosure Standard unpainted 80 x 125 x 57 mm

Declaration of Conformity

Technical Drawing | 3D Data | Assignmentplan | Terminal mounting

Technical data

Height	80 mm
Width	125 mm
Depth	57 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AlSi 12 (Fe)
Colour	Aluminium, unpainted
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
Temperature min.	-30 °C
Temperature max.	90 °C
Seal material	CR-(Chloropren)
Flame spread, sideways	HL 3
Rate of heat dispersion	HL 3
Smoke gas concentration	HL 3

Commercial data

Country of origin	DE
Order unit	1 Piece
Customs tariff number	85369095
Weight	0.449 kg
GTIN	4250157900098


ETIM Classification

ETIM 8	EC000058

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



100110030
Mounting plate for 01.081306



100311010
Outer bracket fastening set M4



100610040
DIN rail 15 for 01.081306