



Cut



Medium Duty

## Cut, oil and abrasion-resistant gloves, granting good grip in dry conditions

- **Optimized durability:** EDGE<sup>®</sup> 48-701 industrial gloves' palm PU coating provides a high level of abrasion protection (ANSI 6), moderate cut resistance (ANSI A2), a good grip in dry environments, and better protection against oil than knitted or cut and sewn safety work gloves
- **Increased protection:** EDGE 48-701 protective gloves provide two levels of cut performance, affording robust, all-round hand protection in mediumweight applications
- **Enhanced features:** A more affordable alternative to medium-duty leather, thick cotton or aramid gloves, EDGE<sup>®</sup> 48-701 high-quality work gloves offer a seamless liner and knitted wrist, which deliver form-fitting comfort, good dexterity and added wrist protection



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

### Applications

- Aeronautics
- Assembly line
- Assembling metal parts and components
- Handling sharp or irregular metal pieces
- Molding
- Plastic injections

### Key Features

- **Palm PU coating:** High level of protection against abrasion and cuts
- **Two levels of cut performance:** For advanced hand protection gloves
- **Seamless liner and knitted wrist:** For flexible and secure work gloves

### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



4342B

### Specifications

| BRAND   STYLE            | DESCRIPTION                                                                                                                                               | Gauge | SIZE               | LENGTH                        | COATING COLOR | PACKAGE                      |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------|-------------------------------|---------------|------------------------------|
| EDGE <sup>®</sup> 48-701 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Polyurethane<br><b>Liner Material:</b> HPPE, Spandex, Polyester<br><b>Cuff Style:</b> Knitwrist | 13    | 6, 7, 8, 9, 10, 11 | 220-270 mm, 8.66-10.63 inches | Black         | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699