

FEATURES

- Hi-flex adjustable gooseneck
- Double shade design for efficient heat dissipation
- Low energy LED bulbs
- High quality build ensures a long work lifespan
- Lightweight for maximum versatility

RS PRO LED Machine Light, 100 → 277 V ac, 3 W, Flexible Neck, 520 Reach, 520mm Arm Length

RS Stock No.: 777-8003



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro, this flexible LED work light gives you light where you need it while keeping your hands free. With a fully adjustable gooseneck, there's no lighting angle that can't be achieved. The gooseneck is also vibration resistant, meaning it can be used with confidence in heavy-machinery environments.

General Specifications

Lamp Type	LED
Light Style	Flexible Arm
Lamp Supplied	Yes
Integral transformer	Yes
Shield Fitted	No
Switch Fitted	No
Shade	Plastic
Neck Length	500mm
Arm Type	Flexible Neck

Electrical Specifications

Mains Plug Type	Type G - British BS1363
Voltage Rating	100V to 240V
Wattage	3W
EU Energy Efficiency Rating	A+
Number of Bulbs	3

Mechanical Specifications

Arm Length	520mm
Cable Length	1.8m
Maximum Reach	520mm
Beam Angle	30°

Protection Category

IP Rating	IP 20
------------------	-------

Approvals

Compliance/Certifications	RoHS Certificate of Compliance , CE Approved
----------------------------------	--



