



Datasheet

ENGLISH

Stock No: 796-666

# RS Pro 40 Bar 2000mm Long Copper Tube, 28mm Outer Diam.



## Product Details

### Copper Tube - Half Hard

- Copper tube to EN 1057-R250 (previous designation BS 2871: Part 1: table X)
- Supplied in 2m lengths in the half hard condition
- Pressure rating (see table) based on tube in half hard condition at 65°C
- Ideal temper for cold bending and forming either on a bending machine or with correct size bending spring
- Can be connected with capillary or compression fittings to BS864: Part 2 or by silver brazing or suitable methods of welding
- General service tube for drinking water conveyance, central heating, sanitation, hot and cold water, gas and various engineering applications

### Specifications:

Nominal Outer Diameter	28mm
Length	2000mm
Wall Thickness	0.9mm
Maximum Working Pressure	40 bar