

## Datasheet

### 7pcs metric nut spinner screwdriver set

RS Stock number 460-1758



#### Material:

Chrome plated (50BV30) for nut spinner blade PP/TPV double injection handle

#### Finish:

Shiny chrome finish for nut spinner blade, lacquer coating Inner hole and red/black colour double injection handle

#### Hardness:

Heat treat to HRC 42-50 degree for nut spinner driver blades

#### Contents:

7pc-nut spinner screwdriver with red/black colour TPV/PP double Injection handle

Size: 4mm (RS stock no. 499-2391)

5mm (RS stock no. 499-2379)

5.5mm (RS stock no. 499-2341)

6.0mm(RS stock no.499-2385)

7.0mm (RS stock no. 499-2329)

8.0mm (RS stock no. 499-2335)

10mm(RS stock no. 499-2357)

(length of blade: 125mm, overall length -245mm Remove the magnet from the steel blade)

**Remark:** Torque dimensions and gauge test meet DIN 3125 standard