

Geberit ACO 203XLplus pressing tool [2], [2XL], 230 V, in case



APPLICATION PURPOSES

- For pressing Geberit pressing systems

CHARACTERISTICS

- Geberit compatibility [2]
- Geberit compatibility [2XL]
- Head rotating
- With Bluetooth® interface for the NovoCheck app
- Hydraulic
- Brushless motor

TECHNICAL DATA

Nominal force	32 kN
Degree of protection	IP20
Nominal voltage	230 V AC
Mains frequency	50–60 Hz
Operating voltage	18 V DC
Rechargeable battery type	lithium-ion battery
Operating temperature	-20 – +60 °C
Operating temperature, rechargeable battery	-10 – +50 °C
Sound pressure level	78 dB(A)
Sound power level max.	89 dB(A)

Vibration emission value max.

2.5 m/s²

SCOPE OF DELIVERY

- Battery-operated pressing tool [2XL] 18 V DC
- Battery charger
- Cleaning agents and lubricants
- 2 lithium-ion rechargeable batteries, 18 V / 5 Ah
- Case

ACCESSORIES

- Geberit carrying belt for case

Art. no.	Compatibility	Protection class	Power consumption W	Plug type	Weight of main element kg
This article is suitable for the following system: Geberit Mepla					
691.229.P5.2	[2] / [2XL]	III	90	BS 1363 A	10.704

Art. no.	Compatibility	Protection class	Power consumption W	Plug type	Weight of main element kg
This article is suitable for the following system: Geberit Mapress					
691.229.P5.2	[2] / [2XL]	III	90	BS 1363 A	10.704