

TF1500S-G1 -827-05

TEC Flex Shortpitch 1500 | LED modules for semi-professional applications



Areas of application

- Cove lighting
- Shelf lighting for retail, shops, supermarkets
- For use in architectural, shop and interior luminaires
- Offices, corridors and residential interiors
- Architectural Integration – e.g. coves, walls

Product family benefits

- High homogeneity thanks to small LED pitch
- Pre-wired LED strip, simple and quick plug-and-play installation
- Easy mounting on many smooth surfaces thanks to self-adhesive tape at the back
- Type of protection: IP00
- Dimmable (with suitable PWM dimming methods)

Product family features

- Flexible and cuttable LED strip
- Luminous flux: up to 1500 lm/m
- Available with color temperature: 2,700K, 3,000 K, 4,000 K, 5,000 K or 6,500 K
- Up to 50,000 hrs lifetime @ tc max
- Recommended in system use with OPTOTRONIC
- Color consistency in 3 SDCM



Technical data

Electrical data

Nominal voltage	24.0 V
Type of current	DC
Nominal wattage per meter	13.2 W
Rated wattage	66.00 W
Input voltage range	23...25 V
Accidental reverse input voltage protection up to	25 V

Photometrical data

Light color LED	White
Color rendering index Ra	80
Luminous flux per meter	1560 lm
Total useful luminous flux	7800 lm
Standard deviation of color matching	≤3 sdc _m
Light color (designation)	White
Color temperature	2740 K
Rated color temperature	2740 K


Light technical data

Rated beam angle (half peak value)	120.00 °
Starting time	< 0.5 s
Warm-up time (60 %)	0.00 s

LED module information

Number of LEDs per meter	140
Number of LEDs per smallest unit	7

Dimensions & weight



Length	5000 mm
Length – smallest unit	50.0 mm
Width	8.00 mm
Height	1.50 mm
Product weight	69.00 g
Cable cross-section, input side	0.5 mm ²

Temperatures & operating conditions

Performance temp. acc. to IEC 62717	35 °C
Temperature range in operation at Tc point	-25...80 °C
Ambient temperature range	-20...+50 °C
Temperature range at storage	-30...85 °C

Lifespan

Rated lamp life time	50000 h
Nominal lamp life time	50000 h
Lumen main.fact.at end of nom.life time	0.70
Number of switching cycles	30000

Capabilities

Dimmable	Yes
Lowest bending radius	20 mm
Self-adhesive	Yes
With connection set	No
With end piece	No

Certificates & standards



Intelligent LED Solutions, Unit 2, Berkshire Business Centre, Berkshire Drive, Thatcham, Berkshire, RG19 4EW
 Telephone: +44 (0)1635 294606 Email: info@i-led.co.uk Web: www.i-led.co.uk
 A division of Intelligent Group Solutions Ltd

Product datasheet

Energy efficiency class	A+
Energy consumption	73 kWh/1000h
Standards	CE/ENEC/EAC
Type of protection	IP00






Logistical data

Commodity code	940540399000
----------------	--------------

Equipment / Accessories

- Simplified connection with optional matching CONNECTsystem
- Flexessories: a complete set of aluminum channels with diffusers and lenses
- Drivers and dimmers: wide selection of OPTOTRONIC 24 V DALI, DMX and BLE

Download Data

File
 User instruction TEC Flex IP00
 Product Datasheet TEC Flex Shortpitch IP00 Product Datasheet (EN)
 Certificates TFX ENEC 130520
 Declarations of conformity TECFlex CE 4210017 300420
 CAD data DWG TEC Flex and TEC Flex Shortpitch

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172134064	TF1500S-G1 -827-05	Shipping carton box 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1344.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.



Intelligent LED Solutions, Unit 2, Berkshire Business Centre, Berkshire Drive, Thatcham, Berkshire, RG19 4EW
Telephone: +44 (0)1635 294606 Email: info@i-led.co.uk Web: www.i-led.co.uk
A division of Intelligent Group Solutions Ltd