



CALIBRATORS

C.A 1621, C.A 1623 and C.A 1631

■ Mains power supply	P01103057
■ MultiFix bag 120 x 245 x 60 mm	P01298075
■ Set of 2 red/black crocodile clips	P01295457Z
■ Set of 2 red/black moulded PVC leads	P01295451Z
■ Set of 2 moulded test probes \varnothing 4 mm	P01295458Z

THERMAL CAMERAS

C.A 1886 and C.A 1888

■ Sun shade	P01651531
■ Photo tripod adapter	P01651526
■ Lens cover	P01651522
■ USB cable	P01295274
■ Battery	P01296041
■ Battery charger	P01296043
■ Mains power supply	P01651527
■ In-vehicle adapter (cigarette lighter)	HX0061

THERMOMETERS

C.A 1821, C.A 1822 and C.A 1823

■ Shockproof sheath + Multifix	P01654252
■ Multifix	P01102100Z
■ Mains adapter	P01651023
■ Bag	P01298075
■ Metal case	P01298071
■ Dataview® software	P01102095
■ Bluetooth BLE / USB modem for PC	P01654253
■ Set of 4 x 1.5 V AA/LR6 rechargeable batteries + charger	HX0053

PH-METER

C.A 10101

■ pH 1.68 NIST* buffer solution, 125 ml	P01700105
■ pH 4.01 NIST* buffer solution, 125 ml	P01700106
■ pH 7.00 NIST* buffer solution, 125 ml	P01700107
■ pH 9.18 NIST* buffer solution, 125 ml	P01700108
■ pH 10.01 NIST* buffer solution, 125 ml	P01700109
■ ORP 468 mV buffer solution, 125 ml	P01700115
■ ORP 220 mV buffer solution, 125 ml	P01700114
■ ORP combination electrode with built-in XRPTST1 temperature sensor	P01710052
■ pH combination electrode with built-in XRGST1 temperature sensor	P01710051
■ Set of 3 plastic beakers	P01710056
■ Shockproof sheath	P01710050
■ 8-pin DIN to BNC & Jack adapter**	P01295501
■ 8-pin DIN to S7 & Jack adapter**	P01295502

*Solution delivered with a quality certificate guaranteeing its compliance with the NIST (National Institute of Standards and Technology) and DIN 19266 standards
 ** Connection adapters for Chauvin Arnoux pH/redox and temperature sensors

CONDUCTIVITY METER

C.A 10141

■ XCP4ST1 conductivity cell with built-in temperature sensor	P01710053
■ 147 μ S/cm conductivity reference standard solution	P01700117
■ 1408 μ S/cm conductivity reference standard solution	P01700118
■ 12.85 mS/cm conductivity reference standard solution	P01700119
■ KCl 1mol/l concentrated reference standard solution	P01700116
■ Set of 3 plastic beakers	P01710056
■ 8-pin DIN to BNC & Jack adapter for conductivity	P01710054
■ 8-pin DIN to S7 & Jack adapter for conductivity	P01710055
■ Shockproof sheath	P01710050

THERMO-HYGROMETER

C.A 1246

■ 75%RH salt cartridge	P01156401
■ 33%RH salt cartridge	P01156402
■ Shockproof sheath + Multifix	P01654252
■ Multifix	P01102100Z
■ Mains adapter	P01651023
■ Bag	P01298075
■ Metal case	P01298071
■ Dataview® software	P01102095
■ Bluetooth BLE / USB modem for PC	P01654253
■ Set of 4 x 1.5 V AA/LR6 rechargeable batteries + charger	HX0053