



VDE Cable Cutter 210mm

VDE CABLE CUTTERS

- VDE (DIN EN/IEC 60900) certified tools. Tested to 10,000 volts and guaranteed to 1,000 volts. Tested against cold to -40°.
- Steel blades are fully forged , hardened and tempered for best durability . Grey titanium surface finish is non reflective and ensures maximum corrossion resistance.
- Induction hardened cutting edges to cut even the hardest of materials.
- Precision machined joint for maximum power transmission with optimum leverage for easy and effortless work.
- Ergonomic grip with softgrip for comfortable handling and good grip.



Article Number	4932464563
Capacity (mm)	-
Capacity pipe [Max. ø mm]	-
Cutting capacity in cable Al and Cu (Max. Ø mm)	25
Cutting capacity in hard wire 1800N mm² (Max. ø mm)	-
Cutting capacity in soft wire 220N mm² (Max. ø mm)	-
Cutting capacity in very hard wire 2300N mm² (Max. ø mm)	-
Length (mm)	210
Pack quantity	1
Total length (mm)	210