

Roof fan, Extract: W: 223 mm, H: 223 mm, RAL 7035, IP54, Airflow: 71 m3/h, Ue AC: 230 V



Model	
product brand name	SIVACON
product designation	Roof fans
type of ventilation	ventilation
fan design withdrawable fan	No
design of the product EMC version	No
General technical data	
A-rated sound power level maximum	42 dB
consumed active power rated value	40 W
cutout width	223 mm
cutout height	223 mm
operating period	37 500 h
rotor speed at 50 Hz rated value	2 700 1/min
rotor speed at 60 Hz rated value	3 200 1/min
type of voltage of the operating voltage	AC
consumed current maximum	0.28 A
operating voltage	
• at AC at 50 Hz rated value maximum	230 V
• at AC at 60 Hz rated value maximum	230 V
Protection class	
protection class IP	IP54
Appearance	
color	light grey
Product details	
product component fan	Yes
Number	
number of ventilators	4
Mechanical Design	
height	287 mm
width	287 mm
depth	104 mm
installation location	roof
fastening method	snap-on mounting
fastening method	
• 19-inch installation	No
• wall mounting	No
net weight	2.6 kg
material	plastic
ambient temperature during operation	
• minimum	-10 °C

• maximum

55 °C

Approvals Certificates

General Product Approval

other

Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6423-5VL44>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6423-5VL44>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6423-5VL44

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

