

Separation horizontal W: 400 mm



Model	
product brand name	SIVACON S4
product designation	subdivision horizontal
design of the surface	zinc plated
General technical data	
design	assembly kit
RAL color number	other
color	miscellaneous
Product details	
product component	
• cable entry	No
• lock	No
Mechanical Design	
height	2 mm
width	400 mm
depth	400 mm
installation width for cabinet installation	400 mm
installation depth for cabinet installation	400 mm
shape of inner subdivisions	
• shape 2a	No
• shape 2b	No
• shape 3a	Yes
• shape 3b	Yes
• shape 4a	No
• shape 4b	No
mounting position	horizontal
net weight	1 kg
material	sheet-steel
Certificates	
reference code according to IEC 81346-2	UC
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

Environment

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ5000-3BA44>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ5000-3BA44>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ5000-3BA44

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/1/2025 

