



2 YEARS
MANUFACTURER
GUARANTEE

450
LUMEN

IP54

70h
MAX

USB RECHARGEABLE

USB POWERBANK

REPLACABLE
LITHIUM-IONEN

Product number
EAN

1173740004
4007123691739

TECHNICAL DATA

Luminous flux	450 lm
Colour temperature	5000 K
Battery capacity	3 Ah
Battery voltage	3.7 V
Battery charging time approx.	3 h
Number of batteries	2

Battery type	18500
Battery technology	Lithium-ion
Protection class	III
Degree of protection (IP)	IP54
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	0.21 kg
Dimension LxWxH (without packing)	8 cm x 8 cm x 5.9 cm

Weight of product (including packaging)	0.3 kg
Dimension LxWxH (incl. packing)	8.8 cm x 8.8 cm x 12.5 cm