

2-1969584-8 ✓ ACTIVE

TE Internal #: 2-1969584-8

TE Internal Description: ASSY,HDR,VERT,GWT,NO-BOSS,DUAL  
ROW,EP2.5

[View on TE.com >](#)



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 2-1969567-8  
HOUSING, PLUG, GWT, DUAL ROW,  
EP2.5


### Customers Also Bought



TE Part #1-640445-0  
10P MTA156 HDR ASSY FL/STR SN



TE Part #1513164-1  
MOLDED STAMPED ANTENNA



TE Part #3-647502-3  
03P MTA100 HDR ASSY,SM,SN, LF




TE Part #1462037-1  
IM01GR=IM RELAY 140mW 3V




TE Part #796136-1  
ASSY, SMT BATTERY CONN



TE Part #2-1761605-5  
IDC LOW PRO HDR 14P RA BLUE



TE Part #2015357-3  
C/A, UMCC/UMCC, 1.37 OD CABLE,  
100MM LON



TE Part #2-1761606-5  
IDC LOW PRO HDR 14P VERT LA



TE Part #2-1734592-6  
FPC CONN. 0.5MM PITCH B/C, 26P

### Documents

#### Product Drawings

[ASSY,HDR,VERT,GWT,NO-BOSS,DUAL ROW,EP2.5](#)

English

#### CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_2-1969584-8\\_B.2d\\_dxf.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1969584-8\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1969584-8\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[7-1773461-6\\_EP2.5\\_Connector\\_Series](#)

English

---

### Product Specifications

[Application Specification](#)

English

---

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

---

### Agency Approvals

[VDE Certificate](#)

English