

## IBG 06OSH

- Part number : IBG 06OSH
- Color code : Blue
- Body : Composite
- Nozzle : Composite
- Triger : Progressive
- Connection : ISO 6150 B 6mm
- Maxi temperature : +70°C
- Mini temperature : -15°C
- Impossible dust intrusion
- Venturi high flow blowing
- Meet OSHA safety standard
- Non scratch body
- Crush resistant
- Flow @ 6 b : 14 m<sup>3</sup>/h - 8.24 cfm
- Sound level : 89 db
- Blowing force : 168 g
- Dynamic pressure : 0.5 b
- Weight : 64 g
- Advised coupling ISI 06

