

Features

- Electrical control with touch button
- 3 speeds
- 3 wind modes: Normal, Natural & Sleep
- 12H timer
- Quiet operation
- Overheat protective motor
- Automatic oscillation up to 85°
- Remote control

RS PRO Tower Fan 23.07m³/min, 3 speed 220-240 V with Type C -European Plug

RS Stock No.: 0735033



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

RS PRO Tower Fan

Keep your space cool, fresh, and comfortable with the RS PRO Tower Fan. This whisper-quiet fan has 3-speed control settings that you can easily adjust using the remote control. The timer feature lets you set it for up to 12 hours. Get ready for some cool relief.

Features and Benefits

- Electrical control with touch button
- 3 speeds
- 3 wind modes for normal, natural & sleep
- Automatic oscillation up to 85°
- 12 hours timer
- With remote control
- Overheat protective motor

General Specifications

Air Flow	23.07 m ³ /min
Fan Type	Tower
Number of Speeds	3
Plug Type	Type C – European Plug
Supply Voltage	220-240 V
Dimensions	240 x 240 x 765 mm
Height	765mm
Special Features	Oscillating
Noise Level	<39dB(1 st setting); <46dB(2 nd setting); <58.6dB(3 rd setting)

Electrical Specifications

Rated Voltage	220-240V
Rated Frequency	50/60Hz
Rating Power	45W
Airflow	1350 rpm
Swinging Head Angle	85°
Weight (G.W)	2.4kgs

Approvals

Declaration	REACH DoC
Certifications	CE, GS
Standards Meet	EN 60335-2-80:2003+A1:2004+A2:2009 EN 60335-1:2012+A11:2014+A13:2017 A1:2019+A14:2019+A2:2019+A15:2021+ A16:2023 EN 62233: 2008

Similar Products

Stock No.	Brand	Product Name	No of Speed	Timmer	Plug Type
227-903	RS PRO	Tower Fan	3 speeds	8 hours	Type G – British 3-pin
227-904	RS PRO	Tower Fan	3 speeds	8 hours	Type C – European Plug