

PVC Cable	No. of Cond.	AWG	Jacket Characteristics	ID Number	Ship Wt. (lbs)	Cond. Colors	Shield	UL	CSA	Type	MSHA	Temp. (°C)
	14	22	7.6mm OD, PVC, BK, 300 V	RF50998-30M RF50998-100M RF50998-200M	7 21 42	BN, OG, TN, BU, GN, PK, RD, WH, BK, RD/BU, GY/BN, YE, GY, VT, Drain (24)	Foil/Drain	•	•	AWM 2517		105° -40°
	15	18 22	8.5 mm OD, PVC, YE, 300 V	RF50625-30M RF50625-100M RF50625-200M	8 27 53	18 = BN, BU, GN/YE, 22 = WH, GN, GY, PK, RD, RD/BU, GY/PK, WH/GN, BN/GN, WH/YE, YE/BN, YE, Drain (22)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	16	22	8.2 mm OD, PVC, BU, 300 V	RF50744-30M RF50744-100M RF50744-200M	8 25 50	WH, BK, GN, RD, OG, BU, BN, YE, VT, GY, PK, TN, WH/BK, WH/GN, WH/RD, WH/BU		•	•	PLTC AWM 2517		105° -30°
	19	18 22	10.0 mm OD, PVC, YE, 300 V	RF50620-30M RF50620-100M RF50620-200M	12 38 75	18 = BN, BU, GN/YE, 22 = WH, GN, YE, GY, PK, RD, BK, VT, GY/PK, RD/BU, WH/GN, BN/GN, WH/YE, YE/BN, WH/GY, GY/BN, Drain)	Foil/Drain	•	•	PLTC AWM 2517	•	105° -30°
	19	22	8.5 mm OD, PVC, BK, 300 V	RF50995-30M RF50995-100M RF50995-200M	9 285 5	18 = BN, BU, GN/YE, 22 = GN, WH/YE, PK, BN/GN, BK, WH/GN, RD/BU, GY/PK, OG, GY, RD, WH, VT, GY/BN, YE, Drain (24)	Foil/Drain	•	•	AWM 2517		105° -40°
	19	18 22	10.4 mm OD, PVC, BK, 300 V	RF50733-30M RF50733-100M RF50733-200M	8 27 54	18 = BN, BU, GN/YE 22 = WH, GN, YE, GY, PK, RD, BK, VT, GY/PK, RD/BU, WH/GN, BN/GN, WH/YE, YE/BN, WH/GY, GY/BN, Drain (20)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	19	18 22	11.2 mm OD, PVC, YE, 300 V	RF51191-30M RF51191-100M RF51191-200M	13 44 87	VT, RD, GY, RD/BU, GN, BU, GY/PK, WH/GN, WH/YE, WH/GY, BK, GN/YE, YE/BN, BN/GN, WH, YE, PK, GY/BN, BN, Drain (20)	Foil/Drain Braid	•	•	PLTC AWM 2517	•	105° -30°
	19	26	7.1 mm OD, PVC, BK, 300 V	RF50873-30M RF50873-100M RF50873-200M	5 173 4	GN/YE, BK, WH/YE, WH/GY, GY/BN, GY/PK, BN, RD/BU, WH/GN, GY, BN/GN, GN, WH, RD, VT, BU, PK, YE, YE/BN, Drain (26)	Foil/Drain	•	•	AWM 2517		105° -40°
	25	22	10 mm OD, PVC, YE, 300 V	RF50631-30M RF50631-100M RF50631-200M	11 34 67	Bn, Bu, WH, Bk, Bn/Rd, Bu/Rd, WH/Rd, Bk/Rd, Bn/Ye, Bu/Ye, WH/Ye, Bk/Ye, Bn/Gy, Bu/Gy, WH/Gy, Bk/Gy, Bn/Gn, Bu/Gn, WH/Gn, Bk/Gn, Bk/Og, WH/Og, Bn/Og, Bu/Og, Gn/Ye, Drain (22)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	26	22	12.4 mm OD, PVC, YE, 600 V	RF51293-30M RF51293-100M RF51293-200M	13 43 86	BN, BU, WH, BK, BN/RD, BU/RD, WH/RD, BK/RD, BN/YE, BU/YE, WH/YE, BK/YE, BN/GY, BU/GY, WH/GY, BK/GY, BN/GN, BU/GN, WH/GN, BK/GN, GY, BK/OG, WH/OG, BN/OG, BU/OG, GN/YE, Drain (22)	Foil/Drain	•	•	AWM 2586		105° -40°

reefast