

# 3GAA131613-BDJ



## General Information

Product ID:	3GAA131613-BDJ
ABB Type Designation:	M3AA 132SC 2
Catalog Description:	No Description Available

## Additional Information

ABB Type Designation:	M3AA 132SC 2
Altitude:	1000 m
Ambient Temperature:	40 °C
Bearing:	6208-2Z/C3
Bearing NDE:	6206-2Z/C3
Country of Origin:	Poland (PL) Sweden (SE)
Customs Tariff Number:	85015220
Direction of Rotation:	Both sides

### Electrical Data:

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	400 V	7.50 kW	2901 r/min	13.00 A	0.910
Y	--	50 Hz	690 V	7.50 kW	2900 r/min	7.00 A	0.920
D	--	50 Hz	415 V	7.50 kW	2909 r/min	12.50 A	0.910

Gross Weight:	64 kg
IC Class:	IC411
IE Class Data (50 Hz):	IE Class IE3 Full Load (100%) 90.5 % Partial Load (75%) 91.7 % Partial Load (50%) 91.6 %
IM Class:	IMB5 IM3001
IP Class:	IP55
Insulation Class:	ICLF
Made To Order:	No
Minimum Order Quantity:	1 piece
Order Multiple:	1 piece
Package Level 1 Units:	0 carton
Poles (High):	2
Product Name:	3-Phase squirrel cage motor
Product Net Weight:	63 kg
Quote Only:	No
Replacement Product ID (NEW):	3GAA131130-BDJ
Selling Unit of Measure:	piece
Standard:	IEC 60034-1
Starting of Motor:	Direct Online
Temperature Class Default:	--
Temperature Rise:	80 K
Terminator Box Location:	D-End top
Two Speed Motor:	No
Type of Duty:	S1
Voltage Code:	D