



# Datasheet

## ECP-60 UK Series

60W Plug-in Power Supply

ENGLISH



### Features:

- Universal input
- No Load power consumption <0.3W
- Compact and light-weight plastic case
- Protections: Short circuit/ Overload
- Class II power supply (without earth pin)
- Pass LPS
- 1 year warranty

Model		816-0090	816-0100	816-0103
Output	DC Voltage	12V	15V	24V
	Rated current	5A	4A	2.5A
	Current range	0 – 5A	0 – 4A	0 – 2.5A
	Rated Power	60W	60W	60W
	Line regulation	±2% max.		
	Ripple & Noise	<10%		
Input	Voltage range	90-264VAC		
	Frequency range	47-63Hz		
	Efficiency	81%		
Protections	Short circuit	Auto recovery		
	Overload	Auto recovery		
Environment	Working temperature	0°C - 40°C		
Safety & EMC	Safety standards	UL60950-1, TUV EN60950-1 approved		
	EMC emission	Compliance to EN55022 Class B, EN61000-3-2, 3		
	EMC Immunity	Compliance to EN61000-2, 3, 4, 6, 8, 11		
Other	Dimensions	96*54*34.7mm (L*W*H)		

