

182.72.104.66303Kegelrollenlager

## Tapered roller bearings 30306-A (Series 303)

main dimensions to DIN ISO 355 / DIN 720, separable,  
adjusted or in pairs

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system

([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

d	30 mm
D	72 mm
T	20,75 mm
a	15 mm ≈
B	19 mm
C	16 mm
Ca	3 mm
min	
Cb	4,5 mm
min	
d <sub>1</sub>	49,3 mm ≈
Da	65 mm
max	
da	40 mm
max	
Da	62 mm
min	
Db	66 mm
min	
db	37 mm
min	
r <sub>1,2</sub>	1,5 mm
min	
r <sub>3,4</sub>	1,5 mm

min	
$r_a$	1,5 mm
max	
$r_b$	1,5 mm
max	
m	0,445 kg $\approx$ Mass
$C_r$	60000 N Basic dynamic load rating, radial
$C_{0r}$	61000 N Basic static load rating, radial
e	0,32
Y	1,9
$Y_0$	1,05
$C_{ur}$	6900 N Fatigue limit load, radial
$n_G$	11000 1/min Limiting speed
$n_B$	7100 1/min Reference speed
	T2FB030 Comparative designation to DIN ISO 355



