



RS Pro 10mm Screwed Shank Slot Drill BS 122/4

RS Stock No: 2348268





Specifications:

2 Flute Screwed Shank Slot Drill Centre Cutting BS 122/4

High Speed Steel: M35 with 5% Cobalt

Order Code	Manufacturers Code	Product Description
	2348268	10mm Screwed Shank Slot Drill





Datasheet RS Pro 10mm Screwed Shank Slot Drill BS 122/4

Technical Specifications:

Code	Dia mm	Flute Lgth	O/A Lgth.	Shank Dia
	10.0	14.5	60.5	10.0