

FEATURES

- **Sintered Bronze Material:** Provides high strength and excellent wear resistance.
- **Flanged Design:** Ensures secure positioning and easy installation.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads effectively.
- **Compact Dimensions:** With a bore size of 10.02 mm and an outside diameter of 13.04 mm, it fits well in tight spaces.

RS PRO 10.02 mm Flanged Plain Bearing

RS Stock No: 528-036



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring smooth rotational or linear motion with minimal friction. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. Its compact design makes it ideal for use in confined spaces, providing reliable support and reducing wear on moving parts.

General Specifications

Bore Size	10.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	13.04 mm
Width	10 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

