

Eaton 248301

Catalog Number: 248301

Eaton Distribution parts. Remote testing module, max. 400V-AC, 0.5A, 0.5HP

General specifications



Product Name	Catalog Number
Eaton Distribution parts	248301
EAN	Product Length/Depth
4015082483012	80 mm
Product Height	Product Width
65.5 mm	8.8 mm
Product Weight	Compliances
0.04 kg	RoHS conform

Product specifications

Used with

Remote testing module

Accessory for residual current circuit breaker

Accessory

Type

Accessory

Accessory for residual

current circuit breaker

Application

Switchgear for industrial and advanced commercial applications

Accessory/spare part type

Remote test module

Equipment heat dissipation, current-dependent

0.02 W

Mounting method

For fitting on left to: FI

Additional equipment required

Monitoring unit

Ambient operating temperature - max

40 °C

Ambient operating temperature - min

-5 °C

Assembly width

0.5 TE

Heat dissipation per pole, current-dependent

0.02 W

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

0

Number of poles at main contact unit - max

0

Number of switches (fault signal)

0

Resources

Drawings

[eaton-dimensions-mas-z-hk.eps](#)

eCAD model

[DA-CE-ETN.Z-FW_050](#)

Installation instructions

[IL019177ZU](#)

mCAD model

[z_fw.stp](#)

[z_fw.dwg](#)

Rated fault current

0.5 A

Voltage type

AC

Functions

With auto test for earth leakage function

Remote drive

Device fitting

Earth leakage switch

Rated operational voltage (Ue) - max

0 V

Rated switch current

0 A

Suitable for current of main contact unit - max

0 A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia