

FEATURES

- Hex nuts metric
- To DIN934
- A2 grade 18/8 stainless steel (Type 304 S15)
- Good resistance to corrosion
- Easy to tighten and loosen

RS PRO Stainless Steel, Hex Nut, M2.5

RS Stock No.: 527-224



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO hex nuts are a six-sided nut that fastens screws and bolts efficiently and securely. They are the most common hexagonal fastener that has internal threads that screw on to the shank of a bolt or a hex cap screw. These metric hex nuts are available in a variety of sizes ranging from M2 to M20.

These RS PRO hex nut fasteners come in various thread sizes:

527-218 – M2

527-224 – M2.5

527-230 – M3

527-246 – M3.5

527-252 – M4

527-268 – M5

527-274 – M6

530-769 – M8

530-775 – M10

530-781 – M12

275-670 – M16

275-686 – M20

General Specifications

Thread Size	M2.5
Material	Stainless Steel
Type	Full
Finish	Plain
Applications	Automotive applications, Construction industry, Machinery & workshops, DIY enthusiasts and professionals, Use in manufacturing sectors such as the food industry, Home

Mechanical Specifications

Width	5mm
Stainless Steel Type	304 (A2)
Specification	DIN 934, ISO 4032
Thickness	1.75mm to 2mm
Thread Pitch	0.45mm
Width Across Corners	5.45mm
Width Across Flats	4.82mm to 5mm



RS Part No.	Thread Size
275670	M16
275686	M20
527218	M2
527224	M2.5
527230	M3
527252	M4
527268	M5
527274	M6
530769	M8
530775	M10
530781	M12
1839045	M12 (19mm)