



Main

Range	Mureva Styl
Range of product	Mureva Styl
Product or component type	Socket-outlet
Device presentation	Mechanism
Outlet poles configuration	2P + E
Outlet standard description	Side earth
Outlet standard deviation	Schuko
Colour tint	White (RAL 9003)

Complementary

Device mounting	Flush Surface
Cover type	With shutter
Socket number	1
Rated current	16 A
[Ue] rated operational voltage	250 V AC
Condition of use	Indoor/outdoor
Material	Brass PP (polypropylene) PC (polycarbonate)
Fixing mode	By screws
Clamping connection capacity	1...2.5 mm ² for rigid cable(s) 1...2.5 mm ² for stranded cable(s) 1...2.5 mm ² for flexible cable(s)
Wire stripping length	13 mm
Height	71 mm
Width	71 mm
Depth	50 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Outlet standard	CEE 7/3
Connections - terminals	Spring clamp terminals

Environment

Quality labels	AENOR EAC
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations