

# Dropped tools are <u>killing</u> productivity, profits and people.

Across many developed countries, dropped objects claim a staggering second place on the leaderboard of workplace killers.

For years, they have posed a difficult hazard to manage. But now, with the support of NLG, we see progressive organisations reject the uncertainty and exposure that threatened them and perhaps for less than the cost of an incident, stop dropped tools forever.

In these pages you'll find a robust range that's designed to perform, tested in the harshest environments and approved by the most demanding Health & Safety professionals. All serial numbered, third-party tested and CE marked to give you that extra piece of mind.

Everything you need to know about dropped objects in one handbook. Download yours free: neverletgo.com/handbook

123

Tool Tethering

A simple system to secure every tool

Learn more: neverletgo.com/123

1

#### Tether Point

Create a secure attachment point on the tool.

2

## Tool Lanyard

Choose the best tool lanyard for your task. Page 11

3

### **Anchor Point**

Select between wristband, belt, harness or fixed point. Page 23



#### Storage

The most advanced tool safety bags and storage equipment designed for working at height.

Page 2



#### Kits

Everything you need to get started, in one pack.

Page 39

# 7 Framework

Every safety leader wants to stop drops. But where do you start?

The NLG 7 Framework™ is a simple step-by-step plan that maps out your journey towards a Zero Drop Zone™. It's used by the world's most progressive organisations to deliver successful dropped object prevention policies, every time. Now you can use it too.

You'll make your workplace even safer — with less hassle. And we're here to guide you.

#### 1 / Discovery Workshop

We'll introduce dropped tool prevention concepts and help identify project scope.

#### 2 / Site Awareness

Together, we'll start engaging users with toolbox talks and free awareness videos and site posters.

#### 3 / Trial

Begin testing a proof of concept with a small team and initiate any bespoke product development.

#### 4 / Policy Template

To save you time, we've compiled everything you need into the most comprehensive Drop Prevention document for you to use.

#### 5 / Training

With a range of training tools from the NLG Academy, it's easy ensure users really understand and provide certificates of competency.

#### 6 / Site Setup

We'll make sure your workplace is ready for Launch Day with supply partners and channels agreed and Tether Stations and Learning Hub Boards in place.

#### 7 / Spread the word

We'll have collected a full pack of photos, information and a project profile along the way - this is a good time to share successes and learnings with the rest of your team (and beyond).

#### Bonus / Free Follow-up Consultation

We'll setup a 90 day review meeting to check everything is running as you expected, address challenges and develop future improvements.

Get started neverletgo.com/star



## Tether Choke™

# 18KG / 39.6LBS 101367

The Tether Choke™ is the heavyweight tether point for big tools and simply cinches around a captive hole or handle.

# Single Arm 101368

Built for big power tools, the Single Securing Arm locks the Tether Choke™ in position and prevents accidental engagement if dropped.

# Twin Arm 101369

The Twin Arms of the Tether Choke™ make it the safest tether point for heavy straight-shafted tools.

#### SPECIFICATION

Optimised V Ring design for extreme performance / Extra high strength webbing delivers ultimate peace of mind / Faster visual inspections with heavyduty contrast stitching / Clever contrast wear indicators ensure early warning of any structural damage / Ergonomic and comfortable grip optimised for use on handles / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 340mm x 25mm







# 360 D Ring Loop

# 3KG / 6.6LBS 101363

The 360 D Ring Loop Tool Tether is the fastest way to create a antitangle tether point on tools with a captive hole or handle.

#### SPECIFICATION

Robust, tangle-free 360 D Ring / Faster visual inspections with contrast stitching / Rugged climbing cord loop allows for quick cinching / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 200mm x 25mm (cord loop: 130mm)





# 360 D Ring Locking Loop Tool Tether

# 3KG / 6.6LBS 101495

The NLG D Ring Locking Loop is a very versatile attachment point with a wide range of uses, from tethering individual bolts to creating load rated tether points on long-handled tools such as nips.

#### **SPECIFICATION**

Unique self-tightening loop design constructed from strong climbing cord / Tough plastic toggle for fast and secure cinching / Robust, tangle-free 360° D Ring / Unique serial number for easy identification and tracking / CE marked / ANSI/ISEA 121-2018 compliant / Dynamic load tested and third-party certified (2:1 safety factor) / Dimensions: 400mm x 25mm [cord loop: 280mm]

# Tape Measure Tether

# 1KG / 2.2LBS 101414

The Tape Measure Tether is specifically engineered to stop falling tape measures and boasts of full adjustability.

#### **SPECIFICATION**

Easy hook and loop adjustability accommodates many tape measure sizes / Sturdy, compact metal belt clip / Strong welded D Ring for quick attachment / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 10cm [H] x 10cm [W] x 7cm [D]



# See more on page $34 \rightarrow$

# Phone Case

# 1KG / 2.2LBS 101383

The Phone Case provides a safe tether point for a tool lanyard whilst retaining the full smartphone functionality, including the camera.

#### SPECIFICATION

Developed to work with all common smartphones including camera compatibility / Soft Touch screen protector retains full touch functionality / Carefully engineered not to compromise audio quality of the phone / In case charging slot allows trouble-free charging cable connection / Non-conductive, lightweight plastic D Ring to tool lanyard attachment / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 180cm (H) x 10cm (W)





# Bungee Tool Lanyard

# 5KG / 11LBS 101372

The Bungee Tool Lanyard is one of the most popular and versatile lanyards for starting tool tethering because of its easy-stretch durable webbing and anti-tangle 360 carabiner.

Lightweight, fully anodised aluminium carabiner with anti-tangle swivel mechanism / High-performance secure locking gate prevents accidental opens / Extended product life with high strength, wear resistant webbing / Rugged climbing cord loop allows for quick cinching / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: Extends 80cm to 120cm



- Serial numbered
- CE Marked
- ANSI/ISFA 121-2018 compliant
- Third-party tested
- High visibility

View more:

neverletgo.com



# Extended Bungee Tool Lanyard

# 5KG / 11LBS 101434

The extra length of the Extended Bungee Tool Lanyard is ideal for reach tasks or working directly from a height safety tool bag.

#### SPECIFICATION

Reduced bungee tension allows for precision control and comfortable handling / Equipped with Quick Clips\*\* for rapid connection and effortless use with gloves / Extended product life with high strength, wear resistant webbing / Faster visual inspections with contrast stitching / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: Extends 100cm to 210cm





# Heavy Duty Bungee Tool Lanyard

# 18KG / 39.6LBS 101373

The Heavy Duty Bungee Lanyard utilises advanced components to deliver unrivalled performance for heavy tools in the most severe environments.

#### SPECIFICATION

Automatic Twistlock carabiner for superior performance and security / Extra high strength webbing delivers ultimate peace of mind / Heavy duty wear protector sleeve provides an additional layer of structural protection / Powerful cinching loop constructed from the world's strongest fibre, Dyneema® / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 80cm [Relaxed] - 130cm [Extended]

# Super Heavy Duty Webbing Lanyard

# 38KG / 83.6LBS 101374

The Super Heavy Duty Tool Lanyard is expertly constructed for the heaviest tools at height, with the extra length making it ideal for working platforms.

#### SPECIFICATION

Automatic Twistlock carabiner for superior performance and security / Extra high strength webbing delivers ultimate peace of mind / Heavy duty wear protector sleeve provides an additional layer of structural protection / Faster visual inspections with heavy-duty contrast stitching / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 190cm





# Super Bungee Tool Lanyard

# 20KG / 44LBS 101419

The NLG Super Bungee Tool Lanyard comfortably stretches over 3 metres allowing for the safe use of heavy tools on platforms when working at height.

#### SPECIFICATION

Low recoil force and extra long reach makes it ideal for elevated platform use / Compact design reduces snagging hazards / Double action automatic locking carabiner for safer securing / Heavy duty wear protector sleeve provides an additional layer of structural protection / Unique serial number for easy identification and tracking / CE marked / ANSI/ISEA 121-2018 compliant / Dynamic load tested and third-party certified [2:1 safety factor] / Dimensions: Extends 160cm to 340cm

# Coiled Tool Lanyard

# 3KG / 6.6LBS 101370

The Coiled Tool Lanyard combines great reach and compact lightweight design with tangle-free double action carabiners.

#### **SPECIFICATION**

Ultra compact design stays neatly out of the way and reduces snagging hazards / Lightweight, fully anodised aluminium carabiner with anti-tangle swivel mechanism / High-performance secure locking gate prevents accidental opens / Dual spin connector design eradicates coil tension during use / Anti-puncture wipe clean sleeve makes cleaning easy / Robust aircraft cable core builds in dependable protection / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 10cm (Relaxed) - 170cm (Extended)





# Extended Coil Tool Lanyard

# 3KG / 6.6LBS 101476

The Extended Coil Tool Lanyard balances lightweight componentry, compact design and exceptional reach to make a great tool lanyard for extended use.

#### **SPECIFICATION**

Low recoil force makes it ideal for extended periods of use / Equipped with Quick Clips™ for rapid connection and effortless use with gloves / PU core is both strong and lightweight / Toughened inspection tag is built for harsh environments / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third-party certified (2:1 safety factor) / Dimensions: Extends from 14cm to 210cm

# Mini Retractable Tool Lanyard

# 0.5KG / 1.1LBS 101480

As the ultimate small retractable tool lanyard, the Mini Retractable Lanyard boasts of a sturdy build quality and strong coated steel cable.

#### SPECIFICATION

Very compact lightweight unit ideal for holster and pouch use / PU coated wire cable is durable and easy to clean / Retractable design reduces snagging hazards in confined spaces / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: Extends from 17cm to 138cm





# Locking Retractable Tool Lanyard

# 1.5KG / 3.3LBS 101389

The low profile Locking Retractable Tool Lanyard features a locking mechanism that allows the lanyard to be locked out while the tool is in use.

#### SPECIFICATION

Locking mechanism allows instant lock-out at any point / Resilient double action stainless steel carabiners / Retractable design reduces snagging hazards in confined spaces / Anti-tamper security markings protect unit integrity / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: Extends from 30cm to 140cm



# Heavy Duty Retractable Lanyard

3KG / 6.6LBS Carabiner 101450 Swivel 101451 Quick Clip™ 101452

The rugged construction of the Heavy Duty Retractable Tool Lanyard makes it fit for the toughest conditions, finished with 3 anti-tangle connector options. A further 2 attachment variants for quick anchorage, make it the most robust retractable system.

#### SPECIFICATION

Fully rubberised ABS housing with improved skeletal frame for the harshest environments / Removable back bridge offers versatility with direct connection to belt or harness / PU coated wire cable is durable and easy to clean / Retractable design reduces snagging hazards in confined spaces / Use 101455 Attachment Loop for fast anchoring / Ideal for fixed anchor point work / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified (2:1 safety factorl / Dimensions: Extends from 20cm to 135cm

# Retractable Attachments

5KG / 11LBS Loop 101455 Quick Clip™ 101456






# Helmet Lanyard

## 101358

The hi-vis, high-stretch elastic design of the Helmet Lanyard make it the cost-effective and comfortable choice to keep hard hats safe at height.

#### **SPECIFICATION**

Hi-vis design provides easy visibility and promotes site compliance / High-stretch elasticated webbing is comfortable and keeps out of the way / Universal compatibility means the lanyard works with any helmet and quickly attaches to the accessory slot or internal harness / Unique Tough Teeth™ clip design is effortless to attach, even with gloves on / Safety breakaway feature ensures user safety near moving parts or machinery / Great value makes it ideal for high volume construction site use / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 40cm x 2cm





# Coiled Helmet Lanyard

# 1KG / 2.2LBS 101399

The Coiled Helmet Lanyard is easy to clean and maintain and provides a compact high-performance alternative to the webbing helmet lanyard.

#### SPECIFICATION

Ultra compact design stays neatly out of the way and reduces snagging hazards / Universal compatibility means the lanyard works with any helmet / Unique Tough Teeth" clip design is effortless to attach, even with gloves on / Safety breakaway feature ensures user safety near moving parts or machinery / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions:



# Adjustable Wristband

# 3KG / 6.6LBS 101365

The Adjustable Wristband pairs with a short coiled tool lanyard to make a popular and functional combination for small hand tools.

#### SPECIFICATION

High comfort durable elasticated webbing provides ergonomic allday comfort / Quickly adjusts to any wrist size with Velcro fastening / Anchor Use - can be utilised as an anchor point on rail or scaffolding / Tether Use - can be used to tether cylindrical objects such as spray cans / Advanced components keep design non-conductive / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions:





# Superlight Safety Tool Belt

# 30KG / 66LBS 101420

A Superlight Safety Tool Belt that comfortably takes on the heavyweight with clever inside size adjustment leaving the outside clean and snag free.

#### SPECIFICATION

Innovative inside size adjustment means one size fits all / Advanced components keep design lightweight, non-conductive and snag free / High strength, wear resistant padded webbing for comfortable all-day use / Heavy duty triple action buckle prevents accidental opens / Unique serial number for easy identification and tracking / CE marked / Load tested and third party certified [4:1 safety factor] / Size Adjustment Range: 30" - 55" [75cm - 140cm]



# Belt Loop Anchor

# 3KG / 6.6LBS 101366

The Belt Loop Anchor makes it effortless to add additional attachment points to your existing work belt.

# BiLock<sup>™</sup> Velcro Anchor

# 3KG / 6.6LBS 101422

The BiLock™ Velcro Anchor utilises clever dual Velcro layering allowing it to be attached to virtually anything and features a docking pad for compatible holsters.



# TriLock<sup>™</sup> Velcro Anchor

# 10KG / 22LBS 101454

The TriLock™ Velcro Anchor utilises clever triple Velcro layering to deliver exceptional tensile strength and make a fast fitting anchor.

# Heavy Duty Anchor Choke™


# 40KG / 88LBS 101494


The Heavy Duty Anchor Choke™ wraps quickly around beams, scaffolding and railings to give a secure anchor point for tool lanyards and buckets.

#### SPECIFICATION

Twin securing arm guards against movement on rails and allows it to be used as a tether point on tools / Optimised V-Ring design for extreme performance / Works with Tether Tape™ / Unique serial number for easy identification and tracking / CE marked / ANSI/ISEA 121-2018 compliant / Dynamic load tested and third-party certified [2:1 safety factor] / Dimensions: 600mm x 25mm (twin arm 150mm)









# Aero Pouch™

# 5KG / 11LBS 101400

New

# Clear Aero Pouch™ 101573

For more information, visit neverletgo.com

Featuring an innovative valve closure system, the Aero Pouch™ is the safest way to keep small parts and fixings at your side when working at height.

#### SPECIFICATION

Unique self-closure valve system is always active to remove chance of user error / Easy access to small parts inside as it does not need to be opened or closed / Dual layer Mega Mesh™ side panels give improved visibility, drainage and ventilation / 2 Integrated anchor points for convenient tool lanvard attachment / Universal fit with Quick Connect™ buckles for easy attachment to belt, harness or rail / Rear D Ring allows for attachment via carabiner if preferred / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 25cm [H] x 20cm [W] x 10cm [D]











# NLG







# Ascent Pouch™

# 5KG / 11LBS 101520

The NLG Ascent Pouch™ redefines the rope access tool bag with a focus on safety and ergonomics.

#### SPECIFICATION

Unique tapered 'D' profile improves capacity, internal visibility and ergonomics / Drop prevention closure system folds neatly out of the way when not required / 4 integrated anchor points for multiple tool lanyard attachment / Rotating twistlock carabiner maintains natural pouch positioning in use / Rear loops offer belt mounting or direct attachment to a harness or rail / Super strong Ascent™ side modules give structural support whilst the external gear loops provide easy staging and extra storage / Removable reinforced base plate protects against piercing from sharp tools / Integrated Drain Vent keeps the pouch in optimal working condition, even in wet weather / Constructed from heavy duty PVC which is both UV stabilised and mildew resistant / Easy wipe clean coating makes light work of maintenance / Structurally engineered to withstand dynamic impact forces / Unique serial number for easy identification and tracking / CE marked / ANSI/ISEA 121-2018 compliant / Load tested and third-party certified (5:1 safety factor] / Dimensions: 20cm x 18cm x 30cm / Capacity: 7 Litre / Internal Anchor Max Load: 5KG (11lbs)

## Hammer Holster

# 5KG / 11LBS 101496

The NLG Hammer Holster overcomes all the associated problems with traditional holsters and tethered tools, so now you can stop lanyards snagging when you are holstering your hammer.

#### SPECIFICATION

Robust cradle arms to quickly catch and secure the hammer / 2 Integrated anchor points for convenient tool lanyard attachment / Universal fit with Quick Connect™ buckles for easy attachment to belt, or harness / Unique serial number for easy identification and tracking / CE marked / ANSI/ISEA 121-2018 compliant / Dynamic load tested and third-party certified [2:1 safety factor] / Dimensions: 18cm [H] x 11cm [W] x 6cm [D] / D Ring Anchor Max Load: 5KG [11lbs]











# Tool Holster

# 5KG / 11LBS 101470







The Tool Holster has been specifically developed for use with tools at height. The unique magnetic plate provides added security for tethered tools and creates an adaptable anchor point for many applications.

#### SPECIFICATION

Unique Ultra-Mag plate ensures added security and holds tools in place once inserted in the holster / Mega Mesh™ lining for improved visibility and wear / 2 Integrated anchor points for convenient tool lanyard attachment / Universal fit with Quick Connect™ buckles for easy attachment to belt,or harness / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified (2:1 safety factor / Dimensions: 22cm [H] x 10cm (W) x 5cm (D) / D Ring Anchor Max Load: 5KG (11lbs) Each

# Tape Measure Tether

# 1KG / 2.2LBS 101414

The Tape Measure Tether is specifically engineered to stop falling tape measures and boasts of full adjustability.

#### SPECIFICATION

Easy hook and loop adjustability accommodates many tape measure sizes / Sturdy, compact metal belt clip / Strong welded D Ring for quick attachment / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 10cm (HI x 10cm (WI x 7cm [DI





#### Radio Pouch

# 1KG / 2.2LBS 101418

The Radio Pouch is the new generation holster for radios of all sizes when working at height.

#### SPECIFICATION

Integrated climbing cord adjustment system accommodates all common radio styles / Intelligent design maintains instant access to radio controls / Dual Mega Mesh™ layering delivers durability and protection whilst ensuring audio quality is not compromised / Radio clip is still accessible and usable thanks to low back feature / Metal-free construction with non-conductive, lightweight ballistic plastic D Ring / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 140mm (H) x 80mm (W) x 50mm (D)

## Phone Case

# 1KG / 2.2LBS 101383

The Phone Case provides a safe tether point for a tool lanyard whilst retaining the full smartphone functionality, including the camera.

#### SPECIFICATION

Developed to work with all common smartphones including camera compatibility / Soft Touch screen protector retains full touch functionality / Carefully engineered not to compromise audio quality of the phone / In case charging slot allows trouble-free charging cable connection / Non-conductive, lightweight plastic D Ring to tool lanyard attachment / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 180cm [H] x 10cm [W]





D RING 1KG / 2.2LBS 101481

## **Tablet Case**

# 3KG / 6.6LBS 101384

The Tablet Case makes it safe and easy to use iPads and other similarly sized electronic equipment when working at height.

#### SPECIFICATION

Designed to work with all popular tablets, such as iPad(R), making it ideal for inspection work / Soft Touch screen protector retains full touch functionality / 3 Camera apertures for compatibility with common tablet camera positions / Non-conductive, lightweight plastic D Ring attachment points / Useful shoulder strap included for convenient carrying / Unique serial number for easy identification and tracking / CE marked / Dynamic load tested and third party certified [2:1 safety factor] / Dimensions: 30cm (H) x 22cm (W)



## Ascent Bucket™

# 125KG / 275LBS 101360

The Ascent Bucket<sup>™</sup> is the world's most advanced lifting and storage bucket for working at height.

#### **SPECIFICATION**

Heavy duty Mega Mesh™ closure system developed for easy viewing of contents even when closed / Drop prevention closure system folds neatly out of the way when not required / Super strong structural webbing sewn through walls and base for ultimate peace of mind / Toughened composite base plate protects against piercing from sharp tools / Coated leather base sleeve delivers extra wear and abrasion resistance / Hoisting strap with burly twistlock carabiner allows secure load control when lifting with a crane or winch, as well as anchoring when stationary / 6 integrated anchor points (5kg each) for multiple tool lanyard attachment / External daisy chain anchor loops for PPE and staging use / Constructed from heavy duty PVC which is both UV stabilised and mildew resistant / Structurally engineered to withstand dynamic impact forces / Easy wipe clean coating makes light work of maintenance / Outer ID pocket for efficient identification / Unique serial number for easy identification and tracking / CE marked / Load tested and third party certified (4:1 safety factor] / Dimensions: 40cm (H) x 32cm (D) / Capacity: 32 Litre











## Ascent Bucket<sup>™</sup> Lid

## 101412

The Ascent Bucket™ Lid is a sensible addition to the Ascent Bucket™, preventing water or fine debris coming in and an extra safety device to stop the contents coming out.

#### SPECIFICATION

Works with Ascent Bucket™ to prevent water ingress in extreme weather / Features sturdy adjustable Quick Connect™ buckles for faster fitting / Constructed from heavy duty PVC which is both UV stabilised and mildew resistant / Structurally engineered to withstand dynamic impact forces / Easy wipe clean coating makes light work of maintenance / Unique serial number for easy identification and tracking / CE marked / Dimensions: 32cm [Diameter] x 9cm [H]





## Ascent Bucket<sup>™</sup> Liner

### 101359

A practical addition to the Ascent Bucket™, the Bucket Liner provides extra protective structure and storage pockets.

#### SPECIFICATION

Works with Ascent Bucket™ to provide rigid body structure and increased content protection / Four internal pockets for handy access and tool organisation / Fast installation with easy Velcro fastening / Simply store flat when not in use to minimise space requirement / Unique serial number for easy identification and tracking / CE marked / Dimensions: 98cm [L] x 26cm [W]

# MEWP Bag

# 30KG / 66LBS 101423

The MEWP Tool Bag is a large tool bag designed to quickly attach an approved rail on an elevated working platform or scaffold.

#### SPECIFICATION

Main compartment divided into 3 organisation pockets making it ideal for shared workspaces / Features lightweight hi vis Mega Mesh<sup>™</sup> lining for improved internal visibility / 4 External pockets for storage of small parts and tools / 7 Integrated anchor points (5kg each) for multiple tool lanyard attachment / TriLock™ Velcro mounting straps for easy attachment to rail or scaffolding / Stabilisation loops attach quickly to a lower rail to provide extra stability / Constructed from heavy duty PVC which is both UV stabilised and mildew resistant / Structurally engineered to withstand dynamic impact forces / Easy wipe clean coating makes light work of maintenance / 3 drain vents built in to keep tool bag ventilated and dry / Hi vis reflective bars improve safety and detection in low light conditions / Unique serial number for easy identification and tracking / CE marked / Load tested and third party certified [4:1 safety factor] / Dimensions: 37cm (H) x 45cm (W) x 15cm (D)











# Linesman Bag

# 30KG / 66LBS 101421



The Linesman Bag is a versatile tool tethering bag with a complete closure system built in and 8 anchor points for tool lanyards.

#### **SPECIFICATION**

Heavy duty drop prevention closure system ensures tools are contained / Top rolls neatly out of the way with intelligent Velcro positioning / Features lightweight hi vis Mega Mesh<sup>™</sup> lining for improved internal visibility / 8 integrated anchor points (5kg each) for multiple tool lanyard attachment / 4 external tool holders provide full tool tethering setup / Constructed from heavy duty PVC which is both UV stabilised and mildew resistant / Structurally engineered to withstand dynamic impact forces / Easy wipe clean coating makes light work of maintenance / Drain vents built in to each pocket to keep tool bag ventilated and dry / Universal fit with Quick Connect™ buckles for easy attachment to belt, harness or rail / Unique serial number for easy identification and tracking / CE marked / Load tested and third party certified (4:1 safety factor) / Dimensions: 35cm [H] x 30cm [W] x 10cm (D) / Capacity: 10.5L





# Tall Tool Bag

# 20KG / 44LBS 101492

The NLG Tall Tool Bag has been designed to keep longer tools safely stored when working at height and provides 6 conveniently integrated anchor points for tool lanyards.

#### SPECIFICATION

Heavy duty drop prevention closure system ensures tools are contained / Features lightweight hi-vis NLG Mega Mesh™ lining for improved internal visibility / 6 integrated anchor points (5KG each) for multiple tool lanyard attachment / 4 external tool holders provide full tool tethering setup / Adjustable sliding centre belt loop to improve compatibility and stability / CE marked / Load tested and thirdparty certified (4:1 safety factor) / Dimensions: 40cm [H] x 20cm [W] x 10cm (D) / Capacity: 8L / D Ring Anchor Max Load: 5KG [11lbs] Each





# Transit Bag

# 50KG / 110LBS 101491


The NLG Transit Bag is a large drop prevention bag that has been developed for storing and lifting large equipment safely when working at height.

#### SPECIFICATION

Large main compartment makes it ideal for large equipment and shared workspaces / Webbing reinforced structure with Dyneema® load stabilisation system / 3 Double action automatic locking carabiners for safer securing / 2 Twistlock carabiners for easy side panel adjustment / 5 Integrated anchor points / Unique serial number for easy identification and tracking / CE marked / Load tested and third-party certified (4:1 safety factor) / Dimensions: 55cm (H) x 72cm (W) x 30cm (D) / Capacity: 100L / D Ring Anchor Max Load: 5KG (11lbs) Each

# Kits

The easy way to start, with everything in one pack. neverletgo.com/kits



# Start raising dropped object awareness on your site...



TOOL TETHERING LEARNING HUB BOARD 100cm x 200cm 101467



Get your own posters, guides, videos and more. For free.

neverletgo.com

# ZEROP DROP ZONE

Let's get to work.
Start stopping
drops today.

neverletgo.com/start



NLG Units 1-2 Abbey Business Park Holton Heath, Poole, BH16 6NN United Kingdom

+44 [0]330 016 0030 team@neverletgo.com