









LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AD2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



SECTION X-X



RECOMMENDED HOLE LAYOUT



OBSOLETE	27.94 [1,100]	25.91 [1,020]	22.86 [900]	9	10	5-104450-9
	25.4 [1,000]	23.37 [920]	20.32 [800]	8	9	5-104450-8
OBSOLETE	22.86 [900]	20.83 [820]	17.78 [700]	7	8	5-104450-7
	20.32 [800]	18.29 [720]	15.24 [600]	6	7	5-104450-6
	17.78 [700]	15.75 [620]	12.7 [500]	5	6	5-104450-5
	15.24 [600]	13.21 [520]	10.16 [400]	4	5	5-104450-4
	12.7 [500]	10.67 [420]	7.62 [300]	3	4	5-104450-3
	10.16 [400]	8.13 [320]	5.08 [200]	2	3	5-104450-2
OBSOLETE	7.62 [300]	5.59 [220]	2.54 [100]	1	2	5-104450-1
	20.32 [800]	18.29 [720]	15.24 [600]	6	7	5-104450-3
	15.24 [600]	13.21 [520]	10.16 [400]	4	5	1-104450-2
	10.16 [400]	8.13 [320]	5.08 [200]	2	3	1-104450-1
	12.7 [500]	10.67 [420]	7.62 [300]	3	4	1-104450-0
	27.94 [1,100]	25.91 [1,020]	22.86 [900]	9	10	104450-9
OBSOLETE	25.4 [1,000]	23.37 [920]	20.32 [800]	8	9	104450-8
	22.86 [900]	20.83 [820]	17.78 [700]	7	8	104450-7
	20.32 [800]	18.29 [720]	15.24 [600]	6	7	104450-6
	17.78 [700]	15.75 [620]	12.7 [500]	5	6	104450-5
	15.24 [600]	13.21 [520]	10.16 [400]	4	5	104450-4
	12.7 [500]	10.67 [420]	7.62 [300]	3	4	104450-3
	10.16 [400]	8.13 [320]	5.08 [200]	2	3	104450-2
	7.62 [300]	5.59 [220]	2.54 [100]	1	2	104450-1

REMARKS	PLATING	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			OWN R BROWN	09FEB01	 TE Connectivity		
			CHK K WRIGHT	09FEB01			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	HEADER ASSY, AMPMODU MTE, VERTICAL, WITH LATCH, SINGLE ROW, .100 CL, .025 SQ POSTS, PCB ORIENTATION, AND RETENTIVE POSTS		
mm				APPRO K WRIGHT			
		PRODUCT SPEC 108-25034		SIZE			
		APPLICATION SPEC —					
MATERIAL	FINISH	WEIGHT	CAGE CODE		DRAWING NO	RESTRICTED TO	
SEE NOTE 6	SEE TABLE	—	A1		00779	 104450	
CUSTOMER DRAWING			SCALE		4:1	SHEET	1 OF 1
			REV		AD		