

Hedge Trimmer LXT®

DUH607

18V, 600 mm, 2700 min⁻¹

Model DUH607 is a 600mm cordless hedge trimmer powered by 18V LXT Li-Ion battery.

Designed to be Lightweight. Large main switch lever. Improved trimming performance.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2700 min ⁻¹
Length Of Blade	600 mm
Max blade opening	15 mm
Tooth Spacing	28 mm
Continuous Use 18V / 3.0 Ah Battery	60 min
Sound Power Level (L _{WA})	84 dB(A)
Sound Pressure Level (L _{pA})	76 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	≤ 2,5 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²
Product Dimensions (L x W x H):	1029 x 209 x 188 mm

User benefits

- Battery protection circuit protects against overloading, over-discharging and over-heating
- Electric brake for maximum productivity and increased operator safety
- Ergonomic soft grip handle provides increased comfort
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Compact and lightweight for reduced operator fatigue
- Anti-vibration structure

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing