

Chemical-resistant butyl gloves, protecting wearers against aggressive hazards in comfort

- **Specialized protection:** AlphaTec® 38-520 industrial gloves offer superb protection against harsh chemical hazards, such as aldehydes, ketones, esters and concentrated mineral acids
- **Reduced allergy risks:** Latex-free by design, these butyl gloves eliminate latex allergy risks
- **Improved ergonomics:** AlphaTec® 38-514 protective gloves are also comfortable, with a naturally curved shape and soft feel, improving workplace safety while making donning and doffing easy
- **Enhanced flexibility:** In addition, their soft butyl formulation heightens their flexibility and dexterity
- **Strengthened grip:** These flexible work gloves also feature a rough finish around the hand area, reinforcing grip performance, for more secure, confident handling

Industries

- Life Sciences
- Oil and gas
- Chemical

Applications

- Chemical Handling
- Opening and draining pumps valves or lines
- Filling, blending and charging of raw materials
- Equipment repair & maintenance



Previously known as: ChemTek™ 38-520

Performance Profile

Key Features

- **Butyl polymer:** Resistance to harsh chemical hazards*
- **Latex-free formulation:** Latex allergy risks eliminated
- **Ergonomic design and soft feel:** Fitted comfort, ease of use *including aldehydes, ketones, esters and concentrated mineral acids
- Product tested to and confirms to the requirements of EN 16350. Inclusion of EN 16350 into product certification still pending



Vulcanization Chemical Accelerators

- 2-Mercaptobenzothiazole disulfide
- Dipentamethylene thriuram disulfide
- Tetramethylthiuram disulfide

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



0493



2010X



ABCIKLPST



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® 38-520	Coating Material: Butyl Polymer	7, 8, 9, 10, 11	355 / 14	Black	• 36 pairs/carton. Individually wrapped with insert

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.