



# vacuum generator

## VN-20-L-T6-PI5-VI6-RO2

Part number: 526131

FESTO

Standard, high suction rate, width 24 mm, T shape with internal thread and open silencer.



## Data sheet

Feature	Value
Nominal size, Laval nozzle	2 mm
Grid dimension	24 mm
Design, silencer	open
Assembly position	Any
Ejector characteristic	High suction flow rate Standard
Integrated function	Open silencer
Design structure	T-shaped
Operating pressure for max. suction rate	3 bar
Operating pressure	1 ... 8 bar
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	188 l/min
Air supply time at nominal operating pressure	0.15 s
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	0 ... 60 °C
Noise level at nominal operating pressure	60 dB(A)
Ambient temperature	0 ... 60 °C
Max. tightening torque	0.8 Nm
Product weight	183 g
Mounting type	with through hole with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	Open silencer
Vacuum connection	G3/8
Material of connecting thread	Wrought aluminium alloy, anodised
Materials note	Free of copper and PTFE Contains PWIS substances Conforms to RoHS
Material seals	NBR
Material receiver nozzle	POM
Material housing	POM-reinforced
Material silencer	Aluminium die cast POM PU foam
Material transmitter nozzle	Wrought Aluminium alloy