

PRODUCT-DETAILS

TC121-TB

PUSH-IN MNT CLAMP .44X.41IN NAT NYL



General Information

Extended Product Type	TC121-TB
Product ID	7TAG009860R0006
EAN	5414363075028
Catalog Description	PUSH-IN MNT CLAMP .44X.41IN NAT NYL
Long Description	Push-In Premountable Clamp, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Width of 11.30mm (0.445 Inches), Height of 10.54mm (0.415 Inches), Clip In Mounting Method

Ordering

EAN	5414363075028
UPC	786210830858

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	8.4 in 213 mm
Package Level 2 Height	7.8 in 198 mm
Package Level 2 Depth / Length	16.2 in 411 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19710520
Material	Nylon/Polyamide 6.6
Mounting Type	Push Mount
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	PLASTIC MOUNTING BASE
Product Type	Snap-In Mounting Base Cap
Special Functions	Snap-In Premountable base for securing wire bundles in cabinets maintains the attractive external appearance of the equipment housing - Snap-Cap.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC121-TB
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC121-TB

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

