



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 9-2176315-8
MELF SMA-A 1M0 1% 50PPM 0204 0.4 W




TE Part # 3-2176315-2
MELF SMA_A 39K 0.1% 15PPM 0204 0.4W



TE Part # 2176316-5
MELF SMA_A 220R 0.1% 15PPM 0207 1W




TE Part # 6-2176314-9
MELF SMA-A 10R 1% 50PPM 0102 0.3 W



TE Part # 9-2176316-4
MELF SMA-A 330K 1% 50PPM 0207 1W

Customers Also Bought



TE Part #2176317-9
MELF SMA-A R22 1% 50PPM 0207 1W



TE Part #176294-1
UNIV POWER CAP HSG 4P P/MOUNT



TE Part #CAT-T3437-ST2999
STD Snap-On Markers



TE Part #1747981-2
Std HDMI, RA, SMT



TE Part #1-2008552-2
CONNECTOR, INLINE VERT SCREWLESS



TE Part #1-826947-0
10P MODU 2 PIN HDR



TE Part #1746540-4
SEMI-HARD TRAY DDR2 SODIMM 4H STD (LATCH



TE Part #3-2176088-2
RP 1J 0.166W 1K62 0.1% 25PPM 1K RL

Documents

Product Drawings

MELF SMA-A R15 1% 100PPM 0207 1W

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-2176317-0_BA.3d_stp.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1-2176317-0_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176317-0_BA.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.