



Cut



Medium Duty

Versatile work gloves offering excellent grip and breathable comfort

- **Optimized protection:** Twice as thin as standard leather with six times the cut protection, these stainless steel and Kevlar® gloves offer an effective protective barrier against snips, screws and sheet metal
- **Improved grip:** ActivArm® 97-002 protective gloves are reinforced with foam nitrile coating around the palm, resulting in highly resilient grip in wet and dry environments
- **Elevated comfort:** Designed with breathable tactility in mind, these industrial gloves possess an ergonomic, well-insulated and dexterous design
- **Enhanced features:** ActivArm® 97-002 safety work gloves feature an adjustable Velcro® cuff enclosure that helps to achieve a snug and secure fit, while keeping out dirt as well as debris for better wrist protection



Industries

- Automotive
- Food Processing
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Picking, fastening components
- Adjusting parts, systems
- Equipment repair & maintenance
- Equipment maintenance and repair
- Adjusting systems and screwing
- Processing sheets, coils, tubes
- Fabricating metal parts, glass sheets

Key Features

- **Stainless steel and Kevlar® fibers:** Excellent cut-resistant gloves
- **Foam nitrile coating:** Breathable work gloves with exceptional grip
- **Ergonomic, seamless knit design:** Improved dexterity and comfort

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X21B

Technologies



INTERCEPT™
Cut Resistance Technology

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm® 97-002	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Nylon, Spandex, Stainless steel, Kevlar® Cuff Style: Velcro®	18	9, 10, 11	226 - 269 mm, 8-10"	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.